

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [39-00-0059](#)
Status: **Active**
Overview: [Mini-Fit Jr.™](#)
Description: Mini-Fit® Female Crimp Terminal, Tin (Sn) over Phosphor Bronze, 18-24 AWG, Reel

Documents:

Drawing (PDF)	Product Specification PS-5556-001 (PDF)
Product Specification PS-51010-003 (PDF)	Product Specification PS-5556-002 (PDF)
Product Specification PS-51010-004 (PDF)	Packaging Specification PK-5556-001 (PDF)
Product Specification PS-51045-003 (PDF)	Test Summary TS-5556-002 (PDF)
Product Specification PS-52252-001 (PDF)	RoHS Certificate of Compliance (PDF)
Product Specification PS-54849-004 (PDF)	

General

Product Family	Crimp Terminals
Series	5556
Application	Power
Crimp Quality Equipment	Yes
Overview	Mini-Fit Jr.™
Packaging Alternative	39-00-0060 (Loose)
Product Name	Mini-Fit®
UPC	800753584662

Physical

Durability (mating cycles max)	30
Gender	Receptacle
Material - Metal	Phosphor Bronze
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Net Weight	0.127/g
Packaging Type	Reel
Plating min - Mating	0.889µm
Plating min - Termination	0.914µm
Termination Interface: Style	Crimp or Compression
Wire Insulation Diameter	1.30-3.10mm
Wire Size AWG	18, 20, 22, 24
Wire Size mm²	N/A

Electrical

Current - Maximum per Contact	9A
Voltage - Maximum	600V

Material Info

Old Part Number	5556PBT
-----------------	---------

Reference - Drawing Numbers

Packaging Specification	PK-5556-001
Product Specification	PS-51010-003, PS-51010-004, PS-51045-003, PS-52252-001, PS-54849-004, PS-5556-001, PS-5556-002, RPS-501566-001, RPS-51010-013, RPS-51045-002, RPS-54269-004, RPS-5557-001, RPS-5557-004, RPS-5557-027, RPS-5557-034, RPS-5557-035, RPS-5557-044, RPS-5557-045, RPS-5557-048, RPS-5557-049, RPS-5557-054
Sales Drawing	SD-5556****
Test Summary	TS-5556-002




image - Reference only

EU RoHS

ELV and RoHS Compliant
REACH SVHC Contains SVHC: No
Low-Halogen Status Low-Halogen

China RoHS



Need more information on product environmental compliance?

Email productcompliance@molex.com
 For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

Search Parts in this Series

[5556Series](#)

Mates With

[5558](#) Mini-Fit® Crimp Male Terminals. Mini-Fit Jr.™ Header, Dual Row, [5566](#) , [5569](#)

Use With

[5557](#) Mini-Fit Jr.™ Receptacle Housing, [30067](#) Mini-Fit® TPA, [42474](#) Mini-Fit® BMI Panel Mount, [5559](#) Mini-Fit Jr.™ Plug Housing, Dual Row

Application Tooling | FAQ

Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.

Japan

Description	Product #
Applicator for M211A Bench Press, 18-24 AWG Wire	0570223000

Side-Feed Applicator 0570223200
For Full-Auto
Machine

This document was generated on 08/15/2013

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION