

Ultra+ (3LR12)

4.5V




Specifications

Classification:	"Alkaline"
Chemical System:	Zinc-Manganese Dioxide (Zn/MnO ₂) No Added Mercury or Cadmium
Designation:	IEC-3LR12
Nominal Voltage:	4.5 volts
Operating Temp:	-18°C to 55°C
Typical Weight:	163 grams
Typical Volume:	77 cubic centimeters
Jacket:	Plastic Label
Terminals:	Spring Clips
Shelf Life:	7 years


Industry Standard Dimensions

(millimeters)




Industry Standard Tests (21°C)

FLASHLIGHT
20 ohm 1 hr/day




RADIO
220 ohm 4 hrs/day



Typical Discharge Characteristics (21°C)

3.9 ohm Continuous Discharge



Important Notice

This datasheet contains typical information specific to products manufactured at the time of its publication.
©Energizer Holdings, Inc. - Contents herein do not constitute a warranty.