

0.75" Diameter Stainless Steel Compression Load Cell

LC302



- ✓ Small 0.75" (19 mm) Dia.
- ✓ Low 0.5" (13 mm) Profile
- ✓ Robotic and Test Bench Applications
- ✓ Built in Load Button for Easy Installation
- ✓ 5-Point Calibration with 59 kOhm Shunt Cal Data

The LC302 Series is only 3/4" (19mm) in diameter and fits in the smallest places. Its high 0.5% accuracy and small package solve many industrial force measurement applications. All stainless steel construction and high quality strain gage assures long term reliability in industrial environments.

The LC302 is also available in metric configurations, with ranges from 0-100 to 0-5,000 N. Please contact our Pressure department for more information.

Product Selection (Specify Model Number)		
Part Number	Description	Qty.
LC302-25	Compression Load Cell 0-25 lb.	
LC302-50	Compression Load Cell 0-50 lb.	
LC302-100	Compression Load Cell 0-100 lb.	
LC302-250	Compression Load Cell 0-250 lb.	
LC302-500	Compression Load Cell 0-500 lb.	
LC302-1K	Compression Load Cell 0-1000 lb.	

