

KEMET Part Number: C322C104K5R5TA
(C322C104K5R5TA)

Capacitor, ceramic, 0.1 uF, +/-10% Tol, 50V, X7R, Lead Spacing=0.2"



Dimensions (in)		
Symbol	Dimension	Tolerance
L	0.2	MAX
H	0.26	MAX
T	0.125	MAX
S	0.2	+/-0.03
LL	0.276	MIN
F	0.02	+0.004/-0.001
K	0.02	
G	0.031	REF

Notes:
-Voltage code from part number
-EIA capacity code

General Information	
Supplier:	KEMET

Specifications	
Capacitance:	0.1 uF
Lead Spacing:	0.2"
Voltage:	50V
Temperature Coefficient:	X7R
Tolerance:	+/-10%
Application:	Commercial Standard
Temperature Range:	-55/+125C
Body Type:	Radial Conformal (Dipped)
Lead Type:	Standard Leads
Lead Form:	Hockey Stick
Termination Type:	Tin

Packaging Specifications	
Package Kind:	Bulk
Package Type:	Bag
Package Quantity:	500