

## M8 Field Attachable Connectors


RSMCK | RKMCK



### Male, 3- and 4-Pole

Field attachable connector, M8 male connector, 3- and 4-pole with threaded joint, assembling with screw terminals.


RSMCK



### Female, 3- and 4-Pole

Field attachable connector, M8 female connector 3- and 4-pole with threaded joint, assembling with screw terminals.


RKMCK




## Pin Assignments

Face Views / M12, Male / Female

3 pole



4 pole





# Be Certain with Belden

## M8 Field Attachable Connectors

RSMCK | RKMCK

### Technical Data

#### Environmental

Degree of protection IP 67 / NEMA 6P  
 Operating temperature range -40°C (-40°F) / +85°C (+185°F)

#### Mechanical

Housing / Molded body PA  
 Insert TPU, self-extinguishing  
 Contact CuZn, pre-nickel and 0.8 microns gold-plated  
 Receptacle shell CuZn, nickel-plated  
 O-ring FKM  
 Mode of connection Screw terminals  
 Connectable conductor 0.14-0.50 mm<sup>2</sup>

#### Electrical

Contact resistance ≤ 5 mΩ  
 Nominal current at 40°C 4 A  
 Nominal voltage 3 poles 60 V  
 4 poles 30 V  
 Rated voltage 3 poles 63 V  
 4 poles 36 V  
 Test voltage 3 poles 1.5 kV eff. / 60 s  
 4 poles 0.8 kV eff. / 60 s  
 Insulation resistance > 10<sup>9</sup> Ω  
 Pollution degree 3

Part Number	Pins	Cable Diameter Range	Characteristics
<b>Male</b>	<b>Female</b>		
RSMCK 3	RKMCK 3	3	Ø 3.5-5.0 mm
RSMCK 4	RKMCK 4	4	Ø 3.5-5.0 mm

