


**KEMET Part Number: C317C332K5R5TA**  
(C317C332K5R5TA)

Capacitor, ceramic, 3300 pF, +/-10% Tol, 50V, X7R, Lead Spacing=0.2"



Dimensions (in)		
Symbol	Dimension	Tolerance
L	0.15	MAX
H	0.23	MAX
T	0.1	MAX
S	0.2	+/-0.03
LL	0.276	MIN
F	0.02	+0.004/-0.001
K	0.02	

Notes:

- Voltage code from part number
- EIA capacity code

**General Information**

Supplier: KEMET

**Specifications**

Capacitance:	3300 pF
Lead Spacing:	0.2"
Voltage:	50V
Temperature Coefficient:	X7R
Tolerance:	+/-10%
Application:	Commercial Standard
Temperature Range:	-55/+125C
Body Type:	Radial Conformal (Dipped)
Lead Type:	pcleads
Lead Form:	Hockey Stick
Termination Type:	Tin

**Packaging Specifications**

Package Kind:	Bulk
Package Type:	Bag
Package Quantity:	500