

H0,14/10 GR SV**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 16

D-32758 Detmold

Germany

Fon: +49 5231 14-0

Fax: +49 5231 14-292083

www.weidmueller.com



- Weidmüller colour code
- in multipack bag (5 x 100 pcs.)

General ordering data

Type	H0,14/10 GR SV
Order No.	9005180000
Version	Wire end ferrule, 0.14 mm ² , 6 mm, Colour code: Weidmüller, Grey (RAL 7035)
GTIN (EAN)	4008190859909
Qty.	500 pc(s).

H0,14/10 GR SV

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 16
 D-32758 Detmold
 Germany
 Fon: +49 5231 14-0
 Fax: +49 5231 14-292083
 www.weidmueller.com

Technical data**Dimensions and weights**

Length	10 mm	Net weight	0.048 g
--------	-------	------------	---------

Product data

Conductor cross-section	0.14 mm ²	Wire connection cross section AWG, max.	AWG 26
Contact surface length (L2)	6 mm	Contact surface diameter (D1)	0.6 mm
Collar diameter (D2)	1.5 mm	Metal sleeve thickness (S1)	0.15 mm
Plastic collar thickness (S2)	0.25 mm		

Classifications

ETIM 3.0	EC000005	UNSPSC	31-16-31-02
eClass 5.1	27-40-02-01	eClass 6.2	27-40-02-01
eClass 7.1	27-40-02-01		

Approvals

Approvals



ROHS	Conform
------	---------