

# Extended-Distance/Quiet Cable with Die-Cast Removable Metallic EMI/RFI Hoods, Stranded, DB25, NEC® CL2, 25 (12 1/2 Pairs)—Pins 1–25, 20-ft. (6.0-m), FF

MFG Part Number: EBN25C-0020-FF



## Description

Extended-Distance/Quiet Cable with Die-Cast Removable Metallic EMI/RFI Hoods, Stranded, DB25, NEC® CL2, 25 (12 1/2 Pairs)—Pins 1–25, 20-ft. (6.0-m), FF

## Quick Facts

- Made for short runs in extra-noisy environments.
- 100% foil shield plus a tinned copper-braid.
- 24 AWG stranded copper conductors.
- Guaranteed for life!

## Further Details

- Protect your data from end to end with a 100% foil shield plus an 85% tinned copper-braided shield.
- Ideal for industrial environments. EMI/RFI-resistant hoods stop damaging noise where cables are most vulnerable—at the connection.
- In extra-quiet environments, use these cables for long runs—up to 500 feet (152.4 m) at 9600 bps.
- Removable hoods enable convenient testing or repinning.
- In extra-quiet environments, use it for long runs up to 500 feet (152.4 m) at 9600 bps.
- Also available with non-removable hoods.

## Technical Specifications for Extended-Distance/Quiet Cable with Die-Cast Removable Metallic EMI/RFI Hoods, Stranded, DB25, NEC® CL2, 25 (12 1/2 Pairs)—Pins 1–25, 20-ft. (6.0-m), FF:

- **Cable Construction** — PVC
- **Conductor Gauge** — 24 AWG (7 x 32) stranded copper
- **Mutual Capacitance** — 12 pF/ft.
- **Resistance** — 30 ohms/1000 ft.
- **Shield** — 100% aluminum foil, 85% tinned copper braid
- **RoHS** — Yes