

Extended-Distance/Quiet Cable with Non-removable EMI/RFI Hoods, Stranded, DB9, Straight-Wired, 9 (4 1/2 Pairs)—All Pins, 2-ft. (0.6-m), MF

MFG Part Number: EGM12D-0002-MF



Description

Extended-Distance/Quiet Cable with Non-removable EMI/RFI Hoods, Stranded, DB9, Straight-Wired, 9 (4 1/2 Pairs)—All Pins, 2-ft. (0.6-m), MF

Quick Facts

- Made for short runs in extra-noisy environments.
- 100% foil shield plus a tinned copper-braid.
- 24 AWG stranded copper conductors.
- Guaranteed for life!

Further Details

- Protect your data from end to end with a 100% foil shield plus an 85% tinned copper-braided shield.
- Ideal for industrial environments. EMI/RFI-resistant hoods stop damaging noise where cables are most vulnerable—at the connection.
- In extra-quiet environments, use these cables for long runs—up to 500 feet (152.4 m) at 9600 bps.
- In extra-quiet environments, use it for long runs up to 500 feet (152.4 m) at 9600 bps.
- Also available with removable hoods.

Technical Specifications for Extended-Distance/Quiet Cable with Non-removable EMI/RFI Hoods, Stranded, DB9, Straight-Wired, 9 (4 1/2 Pairs)—All Pins, 2-ft. (0.6-m), MF:

Cable Construction — PVC

Conductor Gauge — 24 AWG (7 x 32) stranded copper

Mutual Capacitance — 12 pF/ft.

Resistance — 30 ohms/1000 ft.

Shield — 100% aluminium foil, 85% tinned copper braid

RoHS — Yes