

RJ-11 Modular Cable, 6-Wire, Straight-Pinning, 25-ft. (7.6-m)

MFG Part Number: EL06MS-25



Description

RJ-11 Modular Cable, 6-Wire, Straight-Pinning, 25-ft. (7.6-m)

Quick Facts

- High-quality flat-satin cable for data and voice applications.
- Stranded conductor. Guaranteed for life!
-

Further Details

- All-purpose cable is for voice and data applications running up to 1 Mbps.
- Not recommended for Token Ring or Ethernet applications.

Technical Specifications

Cable Construction — Gray flat satin, PVC

Conductor Gauge — 28 AWG

Distance (Maximum) — As per equipment specifications

Mutual Capacitance — 22 pF/ft.

Resistance — 45 ohms/1000 ft.

Connectors — 6-wire