

H0,75/14 W BD**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 16

D-32758 Detmold

Germany

Fon: +49 5231 14-0

Fax: +49 5231 14-292083

www.weidmueller.com



- Linked of wire-end ferrule strips (50 pcs.)
- Weidmüller colour code
- DIN colour code
- other colour code

General ordering data

| | |
|------------|--|
| Type | H0,75/14 W BD |
| Order No. | 9004290000 |
| Version | Wire end ferrule, 0.75 mm ² , 8 mm. Colour code: Weidmüller, White (RAL 9010) |
| GTIN (EAN) | 4008190006778 |
| Qty. | 500 pc(s). |

H0,75/14 W BD

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 16
 D-32758 Detmold
 Germany
 Fon: +49 5231 14-0
 Fax: +49 5231 14-292083
 www.weidmueller.com

Technical data

Dimensions and weights

| | | | |
|--------|-------|------------|---------|
| Length | 14 mm | Net weight | 0.092 g |
|--------|-------|------------|---------|

Product data

| | | | |
|-------------------------------|----------------------|---|---------|
| Conductor cross-section | 0.75 mm ² | Wire connection cross section AWG, max. | AWG 18 |
| Contact surface length (L2) | 8 mm | Contact surface diameter (D1) | 1.2 mm |
| Collar diameter (D2) | 2.8 mm | Metal sleeve thickness (S1) | 0.15 mm |
| Plastic collar thickness (S2) | 0.25 mm | | |

Classifications

| | | | |
|------------|-------------|------------|-------------|
| ETIM 3.0 | EC000005 | UNSPSC | 31-16-31-02 |
| eClass 5.1 | 27-40-02-01 | eClass 6.2 | 27-40-02-01 |
| eClass 7.1 | 27-40-02-01 | | |

Approvals

Approvals



ROHS Conform