

Terminal markers WS 12/5 MC NE WS

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 16
 D-32758 Detmold
 Germany
 Fon: +49 5231 14-0
 Fax: +49 5231 14-292083
 www.weidmueller.com



WS markers are the perfect match for the W-series connectors. Thanks to their system compatibility, the WS tags can also be used with the I-series and the Z-series. The large marking surfaces do not only permit long character strings but also multi-line text. WS markers are ideal for labels with long, customised character strings. Thanks to the proven MultiCard format, printing with laser printer, PrintJet ADVANCED, plotter or MC-Mobilo is possible.

- Can be fitted in strips or individually
- Markers in proven MultiCard format

General ordering data

Type	WS 12/5 MC NE WS
Order No.	1609860000
Version	Terminal markers, MultiCard, 12 x 5 mm, Polyamide 66, Colour: White
GTIN (EAN)	4008190203481
Qty.	720 pc(s).

**Terminal markers
WS 12/5 MC NE WS**

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 16
 D-32758 Detmold
 Germany
 Fon: +49 5231 14-0
 Fax: +49 5231 14-292083
 www.weidmueller.com

Technical data
Dimensions and weights

Length	12 mm	Width	5 mm
Net weight	0.19 g		

Markings

Cadmium	No	Can be labelled with thermal transfer printers	No
Can be printed with plotter	Yes	Can be written with dot-matrix printer	No
Can be written with laser printer	No	Colour	White
Conductor O.D.		Halogen	No
Material	Polyamide 66	Material colour according to resistance code	9
Operating temperature range, max.	100 °C	Operating temperature range, min.	-40 °C
Pin can be written (STI)	Yes	PrintJet	Yes
Silicone	No	Speed marking laser	Yes
UL 94 flammability rating	V-2		

Classifications

ETIM 3.0	EC000761	UNSPSC	30-21-18-07
eClass 5.1	27-14-11-37	eClass 6.2	27-14-11-37
eClass 7.1	27-14-11-37		

Approvals

ROHS	Conform
------	---------

Downloads

DXF	20843_WS_12-5_MC_DXF.dxf
STEP	1609860000_20843_WS_12-5-MC_STP.stp