

Product data sheet

Characteristics

RPZF4

socket RPZ - mixed contact - 16 A - < 250 V -
screw clamp - for relay RPM4..

Product availability: Stock - Normally stocked in distribution facility
Price*: 7.30 USD



Main

Commercial Status	Commercialised
Range of product	Zelio Relay
Product or component type	Socket
Contact terminal arrangement	Mixed
Product compatibility	Plug-in relay RPM (4 C/O)
Shape of pin	Flat
Device short name	RPZ
Sale per indivisible quantity	10

Complementary

[Ith] conventional free air thermal current	16 A
[Ue] rated operational voltage	< 250 V
Tightening torque	<= 8.85 lbf.in (1 N.m) (M3.5 screw(s))
Fixing mode	Clip-on mounting on 35 mm symmetrical DIN rail By screw mounting on panel
Marking	CE
Width	1.97 in (50 mm)
Product weight	0.21 lb(US) (0.094 kg)

Environment

Connections - terminals	Screw clamp terminals, solid cable without cable end 1 x 0.5...2 x 1.5 mm ² / AWG20...AWG16 Screw clamp terminals, flexible cable with cable end 1 x 0.25...2 x 1 mm ² / AWG22...AWG17
Standards	IEC 61984
Product certifications	CSA UL
Ambient air temperature for storage	-40...185 °F (-40...85 °C)
Ambient air temperature for operation	-40...131 °F (-40...55 °C)
IP degree of protection	IP20 conforming to EN/IEC 60529
Dielectric strength	2500 V

Ordering and shipping details

Category	21128 - ZELIO ICE CUBE RELAY ACCESSORIES
Discount Schedule	CP2
GTIN	00785901635697
Nbr. of units in pkg.	10
Package weight(Lbs)	0.21
Product availability	Stock - Normally stocked in distribution facility
Returnability	Y
Country of origin	CN

Contractual warranty

Period	18 months
--------	-----------
