

## Data Sheet

Weller Part no.	T0053280399
Description	Rework station type WDD 161V ESD safe
Comprising	PUD 161V dual output power unit DSX80 desoldering iron AK 20 safety rest WSP80 soldering iron WPH 80 safety rest DX 112 desoldering nozzle DX 113 desoldering nozzle Cleaning tool
Supply voltage	230V 50 Hz
Operating voltage	24V 50Hz
Safety class	1(power unit) 3 (tools)
Rating	160W
Temperature range	50C to 450C
Temperature accuracy	set point +/- 9C
Temperature display	Digital red LED
Temperature set	Up/down push buttons
Temp setback /auto off	selectable
Vacuum	derived from external compressed air source
Air supply	500-600KPA (60 -87 PSI) oil free
Auto tool recognition	Self calibrates for compatible tools up-to 150W rating