

**W-Series, Accessories**  
**WQV 4/10****Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 16  
D-32758 Detmold  
Germany  
Fon: +49 5231 14-0  
Fax: +49 5231 14-292083  
www.weidmueller.com

The versatile and extensive range of products - from 0.05 mm<sup>2</sup> to 300 mm<sup>2</sup> - means that you have diverse options for your applications at your disposal.  
Hardened steel for mechanical strength and high-quality tinned copper for optimum conductivity. All materials comply with RoHS requirements and have been tested to current environment guidelines.

**General ordering data**

Type	WQV 4/10
Order No.	<a href="#">1052060000</a>
Version	W-Series, Accessories, Cross-connector, For the terminals, No. of poles: 10
GTIN (EAN)	4008190054687
Qty.	20 pc(s).

**W-Series, Accessories**  
**WQV 4/10**

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 16  
 D-32758 Detmold  
 Germany  
 Fon: +49 5231 14-0  
 Fax: +49 5231 14-292083  
 www.weidmueller.com

**Technical data**
**Dimensions and weights**

Length	59.4 mm	Width	7.6 mm
Height	18 mm	Net weight	12.15 g

**Temperatures**

Operating temperature		Storage temperature	
Continuous operating temp., min.	-50 °C	Continuous operating temp., max.	100 °C

**Additional technical data**

Explosion-tested version	No	Installation advice	Direct mounting
Version	For the terminals		

**Rated data**

Rated current	41 A
---------------	------

**Material data**

Material	PA 66	Colour	Yellow
UL 94 flammability rating	V-2		

**System specifications**

Product family	W-Series, Accessories
----------------	-----------------------

**Classifications**

ETIM 3.0	EC000489	UNSPSC	30-21-18-01
eClass 5.1	27-14-11-40	eClass 6.2	27-14-11-40
eClass 7.1	27-14-11-40		

**Approvals**

ROHS	Conform
------	---------