
Item no.: 284-681
Product description: 3-CONDUCTOR THROUGH TERMINAL BLOCK



Produkt kann von Bild abweichen / product may differ

Packing unit 25 pieces

RoHS compliant

Product group	1 (Rail Mounted Terminal Blocks)
Cross section [mm ²]	0.2 - 10 mm ²
Cross section [AWG]	24 - 8 AWG
Connection method	CAGE CLAMP® CONNECTION
Measured voltage EN	800 V
Measured shock voltage	8 kV
Pollution degree	3
Current intensity EN	57 A
Weight	31.99 g
Color	gray
Wiring type	Front-entry
No. of connection Points	3
No. of potentials	1
Height	35 mm
Height	1.38 in
Width	10 mm
Width	0.394 in
Depth	97.5 mm
Depth	3.84 in

Strip length from	12 mm
Strip length to	13 mm
Strip length	0.49 in
Mounting	TS 35



Item no.	Admission office	Approval no.	Voltage [V]	Current [A]	Cross section [mm ²]
284-681	ABS	05-HG476175/3-PDA	800	57	10
284-681	CCA	NL5918	800		10
284-681	CSA	154112-1536073	600	54	24-8
284-681	DNV	E-10423	800	57	10
284-681	GL	17295-00HH	800	57	10
284-681	KEMA	2085859.13	800		10
284-681	KR	HMB05880-EL001	800	63	10
284-681	LR	91/20112(E6)	800	57	10
284-681	PRS	TE/1718/880590/08	800		10
284-681	RMR	11130002	800	57	10
284-681	UR	E45172	600	50	24-8

Sorting criteria: admission office - approval number

© WAGO Kontakttechnik GmbH & Co. KG

Specifications are subject to changes and errors may be expected