


Part Number:

N6590286

Type	Size	Rating	Description
Incandescent	T6	28V 40mA	T-1 $\frac{3}{4}$ Midget Groove Lamp



Dimensions in millimetres

TEST VOLTS	CURRENT (mA)			LIGHT OUTPUT (Lm)			LIFE Hours
	Min.	Nom.	Max.	Min.	Nom.	Max.	
28	36	40	44	2.9	3.8	4.7	10,000

Notes:

- |   |                |   |
|---|----------------|---|
| 1 | Base Type      | Nickel plated S5.7s base in accordance with BS EN 60061-1 |
| 2 | Filament Shape | C-2F  |
| 3 | Lamp Marking   | 28V 40mA ink stamped on the base                          |
| 4 | Environmental  | RoHS & REACH SVHC compliant                               |