

HD7L33AE

BRIGHT

- White LEDs provide 58 lumens of light



ECONOMICAL

- Useable light for 14 hours and 15 minutes in flood mode between battery changes (with Energizer® MAX® batteries)



- Lifetime LEDs never need replacing

WEATHERPROOF

- Meets IEC 60529 IPX4 standards
- Continues to operate after exposure to splashing water from all directions



VERSATILE

- 4 light modes – area, spot, flood and red for night vision
- Pivots to direct light where you need it



Lightweight, versatile and comfortable, the Energizer® Pro 7 Headlight keeps your hands free for everything from gathering wood to navigating a trail. The four light modes allow you to choose the best illumination for the task at hand. In addition, this light is water resistant, making it suitable for outdoor activities.



Before Using Your Flashlight:
Please read all instructions and cautionary markings on the package and light

Product Detail:


Designation: Energizer Pro 7 Headlight
Model: HD7L33AE
Color: Blue and Black
Power Source: Three "AAA"
ANSI/NEDA: Series 24
Lamp: Five White LEDs, Two Red LEDs
Lamp Life (hr): Lifetime

Mode:	5 White	3 White	2 White	Red
Lamp Output (lumens):	58	43	29	N/A *
Run Time (h:min):	14:15	16:45	3:45	2:45
Beam Distance (m):	30	18	26	N/A *
Peak Beam Intensity (cd):	225	81	169	N/A *

* Beam Distance and Peak Beam Intensity are not applicable to colored LEDs

Typical Weight: 92 grams with batteries
Dimensions (mm): 45 x 40 x 73

Performance:



Tested according to ANSI/NEMA FL 1 Standards.

Important Notice

This datasheet contains information specific to products manufactured at the time of its publication
Contents herein do not constitute a warranty
 ©Energizer / All Rights Reserved