

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [87438-0243](#)  
**Status:** **Active**  
**Overview:** [Pico-Spox™](#)  
**Description:** 1.50mm Pitch Pico-SPOX™ Wire-to-Board Header, Surface Mount, Right Angle, Shrouded, 2 Circuits, Embossed Tape on Reel, Lead-Free

**Documents:**

<a href="#">3D Model</a>	<a href="#">Packaging Specification SPK-87438-001 (PDF)</a>
<a href="#">Drawing (PDF)</a>	<a href="#">RoHS Certificate of Compliance (PDF)</a>
<a href="#">Product Specification PS-87437 (PDF)</a>	<a href="#">Product Literature (PDF)</a>

**Agency Certification**


UL E29179

**General**

Product Family	PCB Headers
Series	<a href="#">87438</a>
Application	Signal, Wire-to-Board
MolexKits	Yes
Overview	<a href="#">Pico-Spox™</a>
Product Literature Order No	USA-235
Product Name	Pico-SPOX™
UPC	822348438877

**Physical**

Breakaway	No
Circuits (Loaded)	2
Circuits (maximum)	2
Color - Resin	Natural
Durability (mating cycles max)	10
First Mate / Last Break	No
Flammability	94V-0
Glow-Wire Compliant	No
Guide to Mating Part	No
Keying to Mating Part	None
Lock to Mating Part	Yes
Material - Metal	Brass
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Material - Resin	High Temperature Thermoplastic
Net Weight	135.000/mg
Number of Rows	1
Orientation	Right Angle
PCB Locator	No
PCB Retention	None
Packaging Type	Embossed Tape on Reel
Pitch - Mating Interface	1.50mm
Plating min - Mating	2.540µm
Plating min - Termination	2.540µm
Polarized to Mating Part	Yes
Polarized to PCB	Yes
Shrouded	Fully
Stackable	No
Temperature Range - Operating	-55°C to +105°C
Termination Interface: Style	Surface Mount



**EU RoHS**

**ELV and RoHS Compliant**  
**REACH SVHC Contains SVHC: No**  
**Low-Halogen Status**  
**Not Low-Halogen**

**China RoHS**



**Need more information on product environmental compliance?**

Email [productcompliance@molex.com](mailto:productcompliance@molex.com)  
 For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

**Search Parts in this Series**

[87438Series](#)

**Mates With**

[87439-0200](#) Pico-SPOX™ Wire-to-Board Housing

**Use With**

[87421](#) 1.50mm Pico-SPOX™ Crimp Terminal

**Electrical**

Current - Maximum per Contact 2.5A  
Voltage - Maximum 350V

**Material Info****Reference - Drawing Numbers**

Packaging Specification SPK-87438-001  
Product Specification PS-87437, RPS-87437, RPS-87437-001,  
RPS-87437-200  
Sales Drawing SD-87438-\*\*31

This document was generated on 09/05/2013

**PLEASE CHECK [WWW.MOLEX.COM](http://WWW.MOLEX.COM) FOR LATEST PART INFORMATION**