

PRODUCT SPECIFICATION

**Carl
Kammerling**
International

Brand	C.K
Product Range	Precision Electronic Pliers

Range Description

A range of professional quality Electronic pliers and cutters

Features

- Hot drop forged high alloy carbon and chrome vanadium steel for maximum strength
- Precision box joint for smooth and accurate action, longer product life. No adjustments necessary for the life of the pliers. (Models T3744 and T3796 5 are manufactured with a laid in joint)
- Induction hardened blades for a long life
- Mirror polished surface removes the risk of damage through flaking chrome
- Spot welded double leaf springs removes the need for adjustment or replacement





Item Number	Item Description
CKT3771	Precision Roundnose Pliers 120mm
CKT3772	Precision Snipenose Pliers 120mm
CKT3773	Precision Side Cutter Mini Bevel 115mm
TL14002	Precision Side Cutter Full Flush 115mm
TL14000	Precision Side Cutter Mini Bevel 120mm
CKT3775	Precision Side Cutter Mini Bevel 135mm
TL14001	Precision Top Cutter Extra Full Flush 130mm
TL11684	Precision Snipenose Pliers 145mm
CKT3799F	Precision Oblique Cutter Full Flush 110mm

Technical product information	Cutting capacities (mm/AWG)				
	Item	Soft	Med/Hard	Hard	Piano
	T3773	1.5/15	1.0/18	0.4/26	
	T3773EF	1.5/15	0.8/20		
	T3773F	1.5/15	1.0/18		
	T3774	1.5/15	1.0/18	0.4/26	
	T3775	2.0/12	1.5/15	0.7/21	
	T3775EF	2.0/12	1.3/18		
	T3776EF 5	2.0/12	1.6/14		
	T3776F	1.6/14	1.2/16	0.5/24	
	T3778F	1.6/14	1.2/16	0.5/24	
	T3779	2.0/12		1.0/18	0.6/22
	T3780EF	1.5/15	0.6/22		
	T3780F	1.5/15	0.8/20		
	T3781	1.5/15	1.0/18	0.3/28	
	T3786F 4	0.8/20	0.6/22		
	T3880F	1.5/15	0.8/20		
	Wire definitions				
	Piano Wire – Hardened spring steel, 2200 to 2300N/mm ²				
	Hard Wire – Spring Steel, Steel nails, 1600 to 1800N/mm ²				
	Medium/Hard Wire – Iron, nails, 750 to 800N/mm ²				

	Soft Wire – Copper, Aluminium, 220 to 250N/mm ²
Standards compliance	None applicable
User health and safety information	None applicable
RoHS/WEEE compliance	These products do not fall within the scope of RoHS or WEEE regulations
Material safety data	None applicable
Warranty	C.K Precision pliers and cutters are guaranteed for life against imperfect materials or workmanship Normal wear and tear or damage caused through inappropriate use is not covered
Country of origin	Germany