


PRODUCT SPECIFICATION

Brand	C.K
Product Range	PVC pipe cutters

Range Description Ratchet PVC Pipe cutters
Features 430003 <ul style="list-style-type: none"> • Heavy duty cast Aluminium body for strength • Ratchet cutting mechanism for effortless clean cuts • Razor sharp stainless steel blade for corrosion protection and performance • Cable trunking adaptor included for convenience • Cuts a wide variety of plastic and rubber products



Item Number	Item Description
TL10897	Ratchet conduit cutter

Technical product information	<p>430001 Body – Glass fibre reinforced plastic Blade – Stainless steel</p> <p>Capacities: Cuts up to 28mm diameter (1 1/4")</p> <p>Suitable for cutting PVC conduit, Blue water mains plastic pipe, rubber/plastic hose, Pneumatic pipes, electrical sleeving etc.</p>
	<p>430003 Body – Die cast Aluminium Blade – Stainless steel</p> <p>Capacities: Cuts up to 32mm diameter (1 1/4") PVC pipe/conduit Can also be used to cut plastic water pipe, hose pipe, electrical sleeving, cable trunking, etc.</p>

	<p>Note These products are not designed to cut wire, metal or reinforced tubing – attempting to cut such materials will damage the blade</p>
Standards compliance	None applicable
User health and safety information	None applicable
RoHS/WEEE compliance	This product range does not fall within the scope of RoHS or WEEE regulations
Material safety data	None applicable
Warranty	<p>C.K cutters are guaranteed for life against imperfect materials or workmanship</p> <p>The cutter working mechanism and the cutting edge of the blade will wear over time, this is not covered under the terms of the warranty</p>
Country of origin	Taiwan