


# PRODUCT SPECIFICATION

<b>Brand</b>	C.K
<b>Product Range</b>	Ratchet crimping pliers

<b>Range Description</b> Professional quality ratchet crimping pliers	
<b>Features</b>	
<b>TL11631</b> <ul style="list-style-type: none"><li>• High quality carbon steel - for durability</li><li>• High compression pressure – for secure crimping</li><li>• Deadlock system – for safe and precise crimping</li><li>• Quick release lever – for ease of use</li><li>• For boot lace ferrules 0.14 – 2.5mm square AWG 26-14</li><li>• Display packed</li></ul>	
<b>TL15152</b> <ul style="list-style-type: none"><li>• High quality carbon steel - for durability</li><li>• High compression pressure – for secure crimping</li><li>• Deadlock system – for safe and precise crimping</li><li>• Quick release lever – for ease of use</li><li>• For insulated terminals, green red &amp; blue, 0.5-2.5mm square, AWG24-13</li><li>• Display packed</li></ul>	
<b>TL11633</b> <ul style="list-style-type: none"><li>• Cuts strips and crimps all types without change of dies – fast and versatile</li><li>• Lock close facility - for safe storage</li><li>• Pre-set length cutter - 6mm &amp; 12mm for repeatable results</li><li>• Built in wire cutter – for convenience</li><li>• Patented design</li><li>• For modular plugs type 4P2C, 4P4C, 6P4C (RJ11), 6P6C (RJ12), 8P8C (RJ45) &amp; 6P6C/Offset</li><li>• Display packed</li></ul>	
<b>TL11634</b> <ul style="list-style-type: none"><li>• High quality carbon steel - for durability</li><li>• High compression pressure – for secure crimping</li><li>• Deadlock system – for safe and precise crimping</li><li>• Quick release lever – for ease of use</li><li>• For insulated terminals, red, blue &amp; yellow, 0.5-6mm square, AWG20-10</li><li>• Display packed</li></ul>	
<b>TL11635</b> <ul style="list-style-type: none"><li>• High quality carbon steel - for durability</li><li>• High compression pressure – for secure crimping</li><li>• Deadlock system – for safe and precise crimping</li></ul>	

- Quick release lever – for ease of use
- For insulated ferrules 10-25mm square AWG 8-3
- Display packed

**TL11636**

- High quality carbon steel - for durability
- High compression pressure – for secure crimping
- Deadlock system – for safe and precise crimping
- Quick release lever – for ease of use
- For non insulated terminals 1.5 – 10mm square AWG 16-18
- Display packed

**TL11637**

- High quality carbon steel - for durability
- High compression pressure – for secure crimping
- Deadlock system – for safe and precise crimping
- Quick release lever – for ease of use
- For Coax – BNC, TNC, 58, 59, 62, 8X,140, 141, 174 (only 0.128” plugs), 210, 223, 303, 400
- Display packed

**TL11638**

- Cuts strips and crimps without change of dies – fast and versatile
- Lock close facility - for safe storage
- Pre-set length cutter - 6mm & 12mm for repeatable results
- Built in wire cutter – for convenience
- For modular plugs type 6P4C (RJ11), 6P6C (RJ12) & 8P8C (RJ45)
- Display packed

**TL11632**

- High quality carbon steel - for durability
- High compression pressure – for secure crimping
- Deadlock system – for safe and precise crimping
- Quick release lever – for ease of use
- For boot lace ferrules 0.25 – 6.0mm square AWG 20-10
- Display packed

**TL15150**

- High quality carbon steel - for durability
- High compression pressure – for secure crimping
- Deadlock system – for safe and precise crimping
- Quick release lever – for ease of use
- Pressure adjuster – for control
- For MC3 and MC4 Solar PV connectors – Wire sizes 2.5, 4.0 & 6mm<sup>2</sup>
- Display packed

Item Number	Item Description
TL11631	Ratchet crimping pliers for end sleeve ferrules
TL15152	Ratchet crimping pliers for insulated terminals, green, red & blue
TL11633	Ratchet crimping pliers for modular plugs
TL11634	Ratchet crimping pliers for insulated terminals, red, blue & yellow
TL11635	Ratchet crimping pliers for insulated ferrules
TL11636	Ratchet crimping pliers for non insulated terminals

TL11637	Ratchet crimping pliers for Coax
TL11638	Ratchet crimping pliers for modular plugs
TL11632	Ratchet crimping pliers for boot lace ferrules
TL15150	Ratchet crimping pliers for Solar PV MC3 & MC4 connectors

Technical product information	
Standards compliance	None applicable
User health and safety information	Users are advised to wear safety goggles
RoHS/WEEE compliance	This product range does not fall within the scope of RoHS or WEEE regulations
Material safety data	Not applicable
Warranty	C.K tools are guaranteed for life against imperfect materials or workmanship Damage caused through inappropriate use is not covered
Country of origin	Taiwan

## Dimensional details

Item	Product only			
	Width mm	Depth mm	Height mm	Net weight g
TL11631	75	15	195	344
TL15152	70	20	230	517
TL11633	67	20	205	533
TL1163	70	20	230	517
TL11635	70	20	230	517
TL11636	70	20	230	513
TL11637	70	20	230	517
TL11638	75	20	190	296
TL11632	75	18	195	351
TL15150	75	25	230	533