


PRODUCT SPECIFICATION

Brand	C.K
Product Range	Crimping pliers
Catalogue number	3645, 3646 & 30024
Date	10/02/2012

Range Description Crimping pliers for cable links		 <p>TL11629</p> <p>TL11630</p>
Features <ul style="list-style-type: none"> • High alloy carbon steel, drop forged – for long life • Matt chrome plated – for corrosion resistance • Contoured grips with anti-slip horns – for comfort and safety • Specially hardened steel for durability • Four function tool • Soft wire cutting only • Crimping of non-insulated terminals (1.5, 2.5 & 4-6mm) • Crimping of insulated terminals (Red, Blue & Yellow) • Bolt shearing (2.6, 3.0, 3.5, 4.0 & 5.0mm Diameter) • Wire stripping (0.75, 1.0, 1.5, 2.5, 4.0 & 6.0mm²) • Soft grips for prolonged comfortable use 		
Item Number	Item Description	
TL11629	Crimping pliers for cable links on wire 0.25-2.5mm square, AWG 23-13	
TL11630	Crimping pliers for cable links on wire 0.5-16mm square, AWG 20-5	
430024		
Technical product information		
Standards compliance	None applicable	
User health and safety information	None applicable	
RoHS/WEEE compliance	This product range does not fall within the scope of RoHS or WEEE regulations	
Material safety data	None applicable	
Warranty	C.K tools are guaranteed for life against imperfect materials or workmanship	
Country of origin	Germany	