

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [08-58-0110](#)
Status: **Active**
Overview: [KK® 396 RPC Connector System](#)
Description: [KK® Trifurcon™ Crimp Terminal 6438, 18-20 AWG, Reel, Phosphor Bronze Selective Gold \(Au\)](#)

Documents:

Drawing (PDF)	Packaging Specification PK-6838-001 (PDF)
Product Specification PS-40-02 (PDF)	RoHS Certificate of Compliance (PDF)

General

Product Family	Crimp Terminals
Series	6838
Application	Power
Crimp Quality Equipment	Yes
Overview	KK® 396 RPC Connector System
Packaging Alternative	08-58-0111 (Loose)
Product Name	Trifurcon™
UPC	800753614246

Physical

Gender	Female
Material - Metal	Phosphor Bronze
Material - Plating Mating	Gold
Material - Plating Termination	Nickel
Net Weight	0.197/g
Packaging Type	Reel
Plating min - Mating	0.762µm
Plating min - Termination	1.270µm
Termination Interface: Style	Crimp or Compression
Wire Insulation Diameter	2.79mm max.
Wire Size AWG	18, 20
Wire Size mm²	N/A

Material Info

Old Part Number	6838-A(P561)
-----------------	--------------

Reference - Drawing Numbers

Packaging Specification	PK-6838-001
Product Specification	PS-40-02
Sales Drawing	SD-6838



image - Reference only

EU RoHS

ELV and RoHS Compliant
REACH SVHC
Contains SVHC: No
Low-Halogen Status
Low-Halogen

China RoHS



Need more information on product environmental compliance?

Email productcompliance@molex.com
 For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

Search Parts in this Series

[6838Series](#)

Use With

[KK® Crimp Terminal Housing 6442](#) , [41695](#)

Application Tooling | FAQ

Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.

Global

Description **Product #**

Terminator Die	0011402096
Hand Crimper	0638117500
Mini-Mac Applicator	0638885000
for KK® and Trifurcon™ Crimp Terminals	