

Capacitor, Tantalum, General Purpose Radial Conformal (Dipped), 33 uF, +/-10% Tol, 25V@85C, Lead Spacing=5.08 mm



Dimensions (mm)		
Symbol	Dimension	Tolerance
D	8.4	
H	12.7	
F	0.5	+/-0.05
S	5.08	+/-0.38
LL	12.7	+/-1.26

Packaging Specifications	
Package Kind:	Bulk
Package Type:	Bag
Package Quantity:	100

General Information	
Supplier:	KEMET

Specifications	
Value:	33 uF
Voltage DC @ 85C:	25V
Voltage DC @ 125C:	16.5V
Tolerance:	+/-10%
Body Type:	Radial Conformal (Dipped)
Temperature Range:	-55/+125C
Application:	General Purpose
Termination Type:	Tin (Sn)
RoHS:	Yes
Leakage Current:	6.6 uA
Dissipation Factor:	6%