


Capacitor, Tantalum, General Purpose Radial Conformal (Dipped), 1 uF, +/-10% Tol, 35V@85C, Lead Spacing=6.35 mm



Dimensions (mm)		
Symbol	Dimension	Tolerance
D	4.5	
H	8.6	
F	0.5	+/-0.05
S	6.35	+/-0.38
LL	4.75	+/-0.81

Packaging Specifications	
Package Kind:	Bulk
Package Type:	Bag
Package Quantity:	1000

General Information	
Supplier:	KEMET

Specifications	
Value:	1 uF
Voltage DC @ 85C:	35V
Voltage DC @ 125C:	23V
Tolerance:	+/-10%
Body Type:	Radial Conformal (Dipped)
Temperature Range:	-55/+125C
Application:	General Purpose
Termination Type:	Tin (Sn)
RoHS:	Yes
Leakage Current:	0.5 uA
Dissipation Factor:	3%