


Capacitor, Tantalum, General Purpose Radial Conformal (Dipped), 4.7 uF, +/-10% Tol, 35V@85C, Lead Spacing=3.18 mm



**Dimensions (mm)**

Symbol	Dimension	Tolerance
D	5.5	
W	6.35	+/-0.64
H	10.2	
F	0.5	+/-0.05
S	3.18	+/-0.38
LL	4.75	+/-0.81

**Packaging Specifications**

Package Kind:	Bulk
Package Type:	Bag
Package Quantity:	1000

**General Information**

Supplier:	KEMET
-----------	-------

**Specifications**

Value:	4.7 uF
Voltage DC @ 85C:	35V
Voltage DC @ 125C:	23V
Tolerance:	+/-10%
Body Type:	Radial Conformal (Dipped)
Temperature Range:	-55/+125C
Application:	General Purpose
Termination Type:	Tin (Sn)
RoHS:	Yes
Leakage Current:	1.3 uA
Dissipation Factor:	5%