


Number of contacts

6-64



Male header with straight solder pins

Identification	No. of contacts	Part No.						
		Without levers		With short levers		With long levers		
Male header with straight solder pins Length: 2.9 mm	6	09 18 506	└ 924	09 18 506	└ 914	09 18 506	└ 904	
	10	09 18 510	└ 924	09 18 510	└ 914	09 18 510	└ 904	
	14	09 18 514	└ 924	09 18 514	└ 914	09 18 514	└ 904	
	16	09 18 516	└ 924	09 18 516	└ 914	09 18 516	└ 904	
	20	09 18 520	└ 924	09 18 520	└ 914	09 18 520	└ 904	
	24	09 18 524	└ 924	09 18 524	└ 914	09 18 524	└ 904	
	26	09 18 526	└ 924	09 18 526	└ 914	09 18 526	└ 904	
	30	09 18 530	└ 924	09 18 530	└ 914	09 18 530	└ 904	
	34	09 18 534	└ 924	09 18 534	└ 914	09 18 534	└ 904	
	40	09 18 540	└ 924	09 18 540	└ 914	09 18 540	└ 904	
	50	09 18 550	└ 924	09 18 550	└ 914	09 18 550	└ 904	
	60	09 18 560	└ 924	09 18 560	└ 914	09 18 560	└ 904	
	64	09 18 564	└ 924	09 18 564	└ 914	09 18 564	└ 904	
	Male header with straight solder pins Length: 4.5 mm	6	09 18 506	└ 922*	09 18 506	└ 912*	09 18 506	└ 902*
		10	09 18 510	└ 922*	09 18 510	└ 912*	09 18 510	└ 902*
14		09 18 514	└ 922*	09 18 514	└ 912*	09 18 514	└ 902*	
16		09 18 516	└ 922*	09 18 516	└ 912*	09 18 516	└ 902*	
20		09 18 520	└ 922*	09 18 520	└ 912*	09 18 520	└ 902*	
24		09 18 524	└ 922*	09 18 524	└ 912*	09 18 524	└ 902*	
26		09 18 526	└ 922*	09 18 526	└ 912*	09 18 526	└ 902*	
30		09 18 530	└ 922*	09 18 530	└ 912*	09 18 530	└ 902*	
34		09 18 534	└ 922*	09 18 534	└ 912*	09 18 534	└ 902*	
40		09 18 540	└ 922*	09 18 540	└ 912*	09 18 540	└ 902*	
50		09 18 550	└ 922*	09 18 550	└ 912*	09 18 550	└ 902*	
60		09 18 560	└ 922*	09 18 560	└ 912*	09 18 560	└ 902*	
64		09 18 564	└ 922*	09 18 564	└ 912*	09 18 564	└ 902*	

Kinked version on request

\* Not normally kept in stock  
For accessories see page 08.18  
For dimensions see page 08.11

For performance level 3 please specify digit  
For performance level 2 please specify digit  
S4 = 0.76 µm (30 µinch) Au or PdNi equivalent

