

**Alkaline Manganese - Duracell Duralock Plus** **DURACELL**  
Mercury Free



**NEW**

Duracell Plus Power with Duralock Power Preserve™ Technology is our most powerful alkaline battery. Now it comes with a 10-year guarantee in storage. If you're using a device that requires high battery output, Plus Power with Duralock is the way to go.

Voltage (V)	Can Style	Dia	Dimensions (mm)			Weight (g) Approx.
			H	W	D	
1.5	AAA	10.5	44.5	-	-	11
1.5	AA	14.5	50.5	-	-	24
1.5	C	26.2	50	-	-	69
1.5	D	34.2	61.5	-	-	139
9	PP3	-	48.5	26.5	17.5	45

643906

Can Style	Pack Qty.	Order Code	Price Per Pack			
			1+	3+	12+	25+
AAA	8	<b>234-5259</b>	5.67	5.43	5.10	4.91
AA	8	<b>234-5260</b>	5.67	5.43	5.10	4.91
AA	12	<b>234-5257</b>	7.49	7.17	6.75	6.49
C	4	<b>234-5261</b>	4.83	4.62	4.35	4.18
C	8	<b>206-2013</b>	9.50	9.09	8.55	8.22
D	4	<b>234-5263</b>	4.83	4.62	4.35	4.18
D	8	<b>206-2014</b>	9.50	9.09	8.55	8.22
PP3	2	<b>234-5264</b>	4.83	4.62	4.35	4.18
PP3	4	<b>234-5258</b>	8.54	8.18	7.69	7.39