




## PRODUCT SPECIFICATION

**CATALOG NUMBER:** See table below  
**DESCRIPTION:** Outdoor use SJTW cord set  
**APPROVALS:** UL Listed and CSA Certified, or UL/CUL Listed Outdoor Use Cord Set

### CONSTRUCTION PARAMETERS:

Cable type: SJTW  
 Conductor: See table below  
 Jacket material: PVC  
 Overall cable O.D. (nom): See table below  
 Cord rating: Hard Usage per the National Electrical Code  
 Cable legend: Indent print  
 Cable color: See table below



*Note: Plug and connector style may vary*

Attachment plug configuration: NEMA 5-15P  
 Cord connector configuration: NEMA 5-15R  
 Plug and connector material: PVC  
 Plug and connector color: Same as cable color

### ELECTRICAL PROPERTIES:

Cable temperature rating: -40 to +60 °C  
 Nominal operating voltage: 125 VAC  
 Maximum operating current: See table below

Catalog no.	Length	Color	Conductor	Cable O.D. (nom)	Current rating
02304	10 ft	Orange	16/3 26/30 BC	0.315 in	13A
02305	15 ft	Orange			
02306	15 ft	Black			
02307	25 ft	Orange			
02308	50 ft	Orange			
02309	100 ft	Orange			10 A
02407	25 ft	Red	14/3 41/30 BC	0.352 in	15A
02408	50 ft	Red			13A
02409	100 ft	Red			13A

The information presented here is, to the best of our knowledge, true and accurate. However, since conditions of use are beyond our control, all recommendations or suggestions are presented without guarantee or responsibility on our part. We disclaim all liability in connection with the use of information contained herein or otherwise.

This specification is proprietary intellectual property of Coleman Cable Systems. Any information contained herein shall not be disclosed to any party without written consent of Coleman Cable Systems.