



**Tripp Lite**  
1111 West 35th Street  
Chicago, IL 60609 USA  
Telephone: +(773) 869 1234  
E-mail: [saleshelp@tripplite.com](mailto:saleshelp@tripplite.com)

## Model #: TLM626SA

### Safety Surge Suppressor - Rugged, Safe Surge Suppression for Industrial/Automotive/Factory Environments



#### Highlights

- 6 outlets (including transformer outlets and 4 safety covers)
- 6 ft. cord
- 900 joule rating
- Rugged metal case
- \$10,000 [Ultimate Lifetime Insurance](#) (USA and Canada only)

#### Description

This Tripp Lite surge suppressor is designed to provide safe, reliable surge protection in harsh environments. A 900 joule rating can protect connected equipment against even the strongest surges. 6 outlets protect connected equipment against damaging surges, spikes and line noise. Convenient transformer outlets accommodate multiple transformers without blocking other outlets. A 6 ft. grounded cord reaches distant outlets. A lighted on/off switch with integrated circuit breaker provides power control over connected equipment. Breaker protects against dangerous system overload. Protected LED confirms that connected equipment is being protected. 4 safety covers shield unused outlets from debris and accidental contact. A rugged metal case stands up to the harshest environments. Integrated keyhole slots on bottom panel provide convenient wall/desk mounting. Tripp Lite will repair or replace any connected equipment damaged by surges, including direct lightning strikes, up to \$10,000 and for life! As an added safety feature, the surge suppressor's bright yellow color alerts you and others that power cords and tools are in use.

#### Applications

- Industrial
- Automotive
- Factory
- Hardware

#### Package Includes

- TLM626SA SAfety Surge Suppressor
- 4 safety covers
- Owner's manual

#### Features

- 6 OUTLETS protect connected equipment against damaging surges, spikes and line noise
- 6 FT. GROUNDED CORD reaches distant outlets
- LIGHTED ON/OFF SWITCH with INTEGRATED CIRCUIT BREAKER provides power control over connected equipment. Breaker protects against dangerous system overload.
- PROTECTED LED - If this green LED ever goes out, Tripp Lite will replace your surge suppressor under warranty at no charge!
- CONVENIENT TRANSFORMER OUTLETS accommodate multiple transformers without blocking other outlets.
- 4 SAFETY COVERS shield unused outlets from debris and accidental contact.
- RUGGED METAL CASE stands up to the harshest environments.
- INTEGRATED KEYHOLE SLOTS on bottom panel provide convenient wall/desk mounting.
- 900 joules of surge protection
- OSHA color guidelines, outlined in Document 1910.145, alert users to hazardous situations, which may cause minor or moderate injury. This Tripp Lite product complies with those guidelines.

- \$10,000 [ULTIMATE LIFETIME INSURANCE](#) (USA and Canada only)

## Specifications

<b>OVERVIEW</b>	
Intended Application	Industrial/Factory Floor
<b>OUTPUT</b>	
Frequency compatibility	60 Hz
Circuit Breaker (amps)	15
Overload protection	Combo power switch and circuit breaker
Outlet quantity / type	6 NEMA 5-15R
Transformer accommodation	Yes (2)
Outlet safety covers	Yes (4)
Outlet orientation	1 single row of 6
<b>INPUT</b>	
Nominal Input Voltage(s) Supported	120V AC
Recommended Electrical Service	120V (110-125V)
Input connection type	NEMA 5-15P
Input cord length (ft.)	6
Input cord length (m)	1.83
Input cord gauge, type	14 gauge, SJT
Voltage compatibility (VAC)	120
Maximum Surge Amps	45000
<b>LEDS ALARMS &amp; SWITCHES</b>	
Switches	Lighted on/off power switch
Diagnostic LEDs	1 green "protected" LED confirms surge suppression is present
<b>SURGE / NOISE SUPPRESSION</b>	
AC suppression joule rating	900
AC suppression response time	< 1 ns
Protection modes	Includes full normal mode (H-N) and common mode (N-G/H-G) line surge suppression
Clamping voltage (RMS)	150V
EMI / RFI filtering	Up to 20 dB
<b>DATALINE SURGE SUPPRESSION</b>	
Telephone/DSL Protection	No
Cable (Coax) Protection	No
Network (Ethernet) Protection	No

<b>PHYSICAL</b>	
Shipping Dimensions (HWD/in)	13.61 x 4.97 x 2.01
Shipping Dimensions (HWD/cm)	34.57 x 12.62 x 5.11
Shipping weight (lbs)	1.70
Shipping weight (kg)	0.77
Unit Dimensions (HWD/in)	12.23 x 2.30 x 1.28
Unit Dimensions (HWD/cm)	31.06 x 5.84 x 3.25
Unit weight (lbs)	1.46
Unit weight (kg)	0.66
Material of construction	Metal
Integrated keyhole mounting tabs	Yes
Receptacle Color	black
AC line cord color	yellow
Style	Strip
Outlets center to center measurement	Distance between standard outlets = 30.40mm; Distance between transformer and standard outlets = 45mm
Keyhole slot center to center measurement	155mm
<b>CERTIFICATIONS</b>	
UL1449 3rd Edition (AC Suppression)	UL1449 3rd Edition
cUL / CSA (Canada)	cUL
Approvals	cULus, RoHS
<b>WARRANTY</b>	
Product Warranty Period (Worldwide)	Lifetime limited warranty
Connected Equipment Insurance (U.S., Canada & Puerto Rico)	\$10,000 <a href="#">Ultimate Lifetime Insurance</a>

More information, including related products, owner's manuals, and additional technical specifications, can be found online at [www.tripplite.com/en/products/model.cfm?txtModelID=3667](http://www.tripplite.com/en/products/model.cfm?txtModelID=3667).

Copyright © 2013 Tripp Lite. All rights reserved. All trademarks are the sole property of their respective owners. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Photos may differ slightly from final products.