



**Tripp Lite**  
1111 West 35th Street  
Chicago, IL 60609 USA  
Telephone: +(773) 869 1234  
E-mail: [saleshelp@tripplite.com](mailto:saleshelp@tripplite.com)

## Model #: TLM812GF

### Power It! Safety Power Strip with 8 Outlets and 12-ft. Cord with GFCI Plug



#### Highlights

- 8 outlets (including transformer outlets and 4 safety covers)
- 12 ft. cord with GFCI plug
- Cord wrap with hang holes
- Rugged metal case

#### Description

This Tripp Lite power strip is designed to safely distribute power to connected equipment in harsh environments. It provides a convenient source for multiple outlets wherever they're needed. 8 outlets distribute AC power to a wide range of power tools, pumps, machinery, air compressors and more. Convenient transformer outlets accommodate multiple transformers without blocking other outlets. A 12 ft. grounded cord with integrated cord clip reaches distant outlets. A GFCI plug protects users from electrical shock in wet or humid environments. A lighted on/off switch provides power control over connected equipment. 4 safety covers shield unused outlets from debris and accidental contact. A rugged metal case stands up to the harshest environments. Built-in cord wrap with hang holes provides convenient cord management. Integrated keyhole slots on bottom panel provide convenient wall/desk mounting. Its bright yellow color alerts you and others that power cords and tools are in use.

#### Applications

- Industrial
- Automotive
- Factory
- Hardware

#### Package Includes

- TLM812GF Safety Power Strip
- 4 safety covers
- Owner's manual

#### Features

- 8 outlets distribute AC power to a wide range of power tools, pumps, machinery, air compressors and more.
- Convenient transformer outlets accommodate multiple transformers without blocking other outlets.
- A 12 ft. grounded cord with integrated cord clip reaches distant outlets.
- A GFCI plug protects users from electrical shock in wet or humid environments.
- A lighted on/off switch with integrated 15 amp circuit breaker provides power control and overload protection over connected equipment.
- 4 safety covers shield unused outlets from debris and accidental contact.
- A rugged metal case stands up to the harshest environments.
- Built-in cord wrap with hang holes provides convenient cord management.
- Integrated keyhole slots on bottom panel provide convenient wall/desk mounting.

- Its bright yellow color alerts you and others that power cords and tools are in use.
- OSHA color guidelines, outlined in Document 1910.145, alert users to hazardous situations, which may cause minor or moderate injury. This Tripp Lite product complies with those guidelines.

## Specifications

<b>OVERVIEW</b>	
<b>Intended Application</b>	Safety; Industrial/Factory Floor
<b>OUTPUT</b>	
<b>Frequency compatibility</b>	60 Hz
<b>Circuit Breaker (amps)</b>	15
<b>Overload protection</b>	GFCI plug
<b>Outlet quantity / type</b>	8 NEMA 5-15R
<b>Transformer accommodation</b>	Yes (3)
<b>Outlet safety covers</b>	Yes (4)
<b>Outlet orientation</b>	1 bank of 5, 1 bank of 3 (transformer outlets)
<b>INPUT</b>	
<b>Nominal Input Voltage(s) Supported</b>	120V AC
<b>Recommended Electrical Service</b>	120V, 15A
<b>Input connection type</b>	GFCI 5-15P
<b>Input plug features</b>	Integrated cord clip plus GFCI breaker
<b>Input cord length (ft.)</b>	12
<b>Input cord length (m)</b>	3.66
<b>Input cord gauge, type</b>	14 gauge, SJT
<b>Voltage compatibility (VAC)</b>	120
<b>LEDS ALARMS &amp; SWITCHES</b>	
<b>Switches</b>	Combination AC circuit breaker and 2 position red illuminated on/off power switch
<b>PHYSICAL</b>	
<b>Shipping Dimensions (HWD/in)</b>	12.43 x 11.44 x 2.17
<b>Shipping Dimensions (HWD/cm)</b>	31.57 x 29.06 x 5.51
<b>Shipping weight (lbs)</b>	5.18
<b>Shipping weight (kg)</b>	2.35
<b>Unit Dimensions (HWD/in)</b>	10.26 x 5.13 x 1.57
<b>Unit Dimensions (HWD/cm)</b>	26.06 x 13.03 x 3.99
<b>Unit weight (lbs)</b>	4.63
<b>Unit weight (kg)</b>	2.10

<b>Material of construction</b>	All-metal
<b>Integrated keyhole mounting tabs</b>	Yes
<b>Receptacle Color</b>	black
<b>AC line cord color</b>	yellow
<b>Style</b>	Strip
<b>Outlets center to center measurement</b>	Distance between standard outlets = 25.40mm; Distance between transformer outlets = 50.80mm
<b>Keyhole slot center to center measurement</b>	145mm
<b>CERTIFICATIONS</b>	
<b>Approvals</b>	cULus, RoHS
<b>WARRANTY</b>	
<b>Product Warranty Period (Worldwide)</b>	Lifetime limited warranty

More information, including related products, owner's manuals, and additional technical specifications, can be found online at [www.tripplite.com/en/products/model.cfm?txtModelID=3673](http://www.tripplite.com/en/products/model.cfm?txtModelID=3673).

Copyright © 2013 Tripp Lite. All rights reserved. All trademarks are the sole property of their respective owners. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Photos may differ slightly from final products.