



Tripp Lite
1111 West 35th Street
Chicago, IL 60609 USA
Telephone: +(773) 869 1234
E-mail: saleshelp@tripplite.com

Model #: TLP808TELV

8-outlet, 8-ft cord, 2160 joule, RJ11 and coaxial protection - Protect It! Surge Suppressor



Highlights

- 8 outlets / 8-ft. cord
- 2160 joule rating
- 2.2GHz gold coaxial surge protection
- Modem/fax surge protection
- \$150,000 [Ultimate Lifetime Insurance](#) (USA & Canada only)

Description

Tripp Lite's TLP808TELV surge suppressor has 8 outlets, an 8-ft. cord with a space-saving right-angle plug, and diagnostic LEDs. The unit has a surge suppression rating of 2160 joules to handle the strongest surges. Built-in RJ11 jacks prevent surges from damaging your modem/fax/phone equipment. Built-in 2.2GHz gold coax jacks prevent surges from damaging your cable/satellite equipment. \$150,000 [Ultimate Lifetime Insurance](#) (USA & Canada only).

Applications

- Ideal for home computers, TV/VCR/DVD players, stereos and other important electrical equipment

Package Includes

- TLP808TELV
- 6-ft. telephone cord
- 6-ft gold coax cable
- Instruction manual with warranty information

Features

- 8 outlets with integrated child safety covers; charcoal gray housing
- 8-ft. cord with space-saving right-angle plug
- Built-in RJ11 jacks (1 in/2 out) prevent surges from damaging your modem/fax/phone equipment; 6-ft. telephone cord included
- Built-in 2.2GHz gold coax jacks prevent surges from damaging your cable/satellite equipment; 6-ft. gold coax cable included
- Surge suppression rating: 2160 joules
- EMI/RFI noise filtering
- Can accommodate up to 3 transformers without blocking remaining outlets
- \$150,000 Ultimate Lifetime Insurance (USA and Canada Only)
- Diagnostic LEDs indicate protection present & ground present
- Audible alarm notifies user when the unit is damaged and needs to be replaced
- Keyhole supports for wall mounting
- Lighted power switch

Specifications

OVERVIEW

| | |
|------------------------------------|--|
| Intended Application | Home/Office, Audio/Video |
| OUTPUT | |
| Frequency compatibility | 50 / 60 Hz |
| Output watts | 1800 |
| Circuit Breaker (amps) | 15 |
| Outlet quantity / type | 8 NEMA 5-15R |
| Transformer accommodation | Supports 3 large transformer plug accessories without covering remaining outlets, accepts up to 6 transformers total |
| Outlet safety covers | Includes built-in sliding outlet safety covers |
| Outlet orientation | Single row of 5, plus a second row of 3 for transformer accommodation |
| INPUT | |
| Nominal Input Voltage(s) Supported | 120V AC |
| Recommended Electrical Service | 120V (110-125V) |
| Input connection type | NEMA 5-15P |
| Input plug features | Space-saving right angle input plug |
| Input cord length (ft.) | 8 |
| Input cord length (m) | 2.44 |
| Input cord gauge, type | 14 gauge, SJT |
| Voltage compatibility (VAC) | 120 |
| Maximum Surge Amps | 144000 |
| LEDS ALARMS & SWITCHES | |
| Switches | Combination AC circuit breaker and 2 position red illuminated on/off power switch |
| Diagnostic LEDs | Built-in LEDs confirm suppressor "protection present" (green) and "grounded" (red) status |
| SURGE / NOISE SUPPRESSION | |
| AC suppression joule rating | 2160 |
| AC suppression response time | < 1 ns |
| Protection modes | Includes full normal mode (H-N) and common mode (N-G / H-G) line surge suppression |
| Clamping voltage (RMS) | 150 |
| UL1449 let through rating | 330/400/400 |
| EMI / RFI filtering | Up to 40 dB |
| DATALINE SURGE SUPPRESSION | |
| Telephone/DSL Protection Details | 1 line |
| Cable (Coax) Protection | Yes |
| Cable (Coax) Protection Details | 1 line |

| | |
|---|---|
| Network (Ethernet) Protection | No |
| PHYSICAL | |
| Shipping Dimensions (HWD/in) | 11.41 x 8.66 x 2.04 |
| Shipping Dimensions (HWD/cm) | 28.98 x 22.00 x 5.18 |
| Shipping weight (lbs) | 2 |
| Shipping weight (kg) | 0.91 |
| Unit Dimensions (HWD/in) | 4.86 x 9.55 x 1.51 |
| Unit Dimensions (HWD/cm) | 12.34 x 24.26 x 3.84 |
| Unit weight (lbs) | 1.9 |
| Unit weight (kg) | 0.86 |
| Material of construction | Plastic |
| Integrated keyhole mounting tabs | Keyhole mounting tabs enable wall mounting |
| Housing Color | Dark Gray |
| Receptacle Color | Dark Gray |
| AC line cord color | Dark Gray |
| Style | Strip |
| Outlets center to center measurement | Distance between standard outlets = 28.5mm; Distance between transformer outlets = 57mm |
| Keyhole slot center to center measurement | Distance between horizontal tabs = 75mm; Distance between vertical tabs = 41.6mm |
| SPECIAL FEATURES | |
| Additional Information | Pair of phone line output jacks serve as a line splitter to enable the protection of two devices sharing a single dialup phone line |
| Right-Angle Plug | Yes |
| CERTIFICATIONS | |
| UL1449 3rd Edition (AC Suppression) | UL1449 3RD EDITION |
| UL1363 (Power Tap) | UL1363 |
| UL497A (Communications) | UL497A |
| FCC Part 68 (Communications) | FCC Part 68 |
| cUL / CSA (Canada) | cUL |
| Industry Canada (Communications) | Industry Canada |
| Approvals | Exceeds IEEE 587 category A&B specifications |
| WARRANTY | |

| | |
|---|---|
| Product Warranty Period (Worldwide) | Lifetime limited warranty |
| Connected Equipment Insurance (U.S., Canada & Puerto Rico) | \$150,000 Ultimate Lifetime Insurance |

More information, including related products, owner's manuals, and additional technical specifications, can be found online at www.tripplite.com/en/products/model.cfm?txtModelID=142.

Copyright © 2013 Tripp Lite. All rights reserved. All trademarks are the sole property of their respective owners. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Photos may differ slightly from final products.