



**Tripp Lite**  
1111 West 35th Street  
Chicago, IL 60609 USA  
Telephone: +(773) 869 1234  
E-mail: [saleshelp@tripplite.com](mailto:saleshelp@tripplite.com)

## Model #: PS6

### Waber-by-Tripp Lite 6-outlet Power Strip with 4-ft. Cord



#### Highlights

- 6 outlets
- 4-ft. cord
- 9.5-inch length
- Master on/off switch

#### Description

The Waber-by-Tripp Lite PS6 Power Strip offers a convenient method of power distribution in workbench, wallmount or floor mount applications. Includes 6 NEMA 5-15R output receptacles, 4-ft. AC line cord and keyhole mounting tabs for installation in a wide variety of applications. Corded, multi-outlet strip reduces cabling clutter and enables the connection of multiple electrical devices to a single AC wall socket. Unfiltered electrical pass-through makes the PS6 ideal for distributing alternate waveform UPS or generator power. Features power switch, circuit breaker and attractive gray color scheme.

PLUG/OUTLETS - Input: NEMA 5-15P/Output: 6 NEMA 5-15R

ELECTRICAL - 120VAC, 50/60Hz, 15A (Requires standard NEMA 5-15R wall receptacle)

FORMAT - Corded power distribution strip

#### Applications

- Offers multiple outlet power distribution in workbench, wallmount or floor mount applications. Unfiltered electrical pass-through makes the PS6 ideal for distributing alternate waveform UPS or generator power to protected equipment.

#### Package Includes

- PS6 Power Strip
- Warranty information
- Instruction manual

#### Features

- Multi-outlet power strip offers convenient power distribution in workbench, wallmount or floor mount applications
- Includes 6 NEMA 5-15R output receptacles
- Power switch
- 15A circuit breaker
- Keyhole mounting tabs for installation in a wide variety of applications
- UL1363 (USA), cUL (Canada)
- 15A power handling capacity
- 4-ft. AC line cord

## Specifications

OVERVIEW	
Intended Application	Home/Office; Industrial/Factory Floor
OUTPUT	
Frequency compatibility	50 / 60 Hz
Circuit Breaker (amps)	15
Outlet quantity / type	6 NEMA 5-15R
Outlet orientation	Single row of 6
INPUT	
Nominal Input Voltage(s) Supported	120V AC
Recommended Electrical Service	15A 120V
Input connection type	NEMA 5-15P
Input cord length (ft.)	4
Input cord length (m)	1.22
Input cord gauge, type	14 gauge, SJT
Voltage compatibility (VAC)	120
LEDS ALARMS & SWITCHES	
Switches	Master on/off switch with separate circuit breaker
PHYSICAL	
Shipping Dimensions (HWD/in)	1.77 x 3.54 x 10.63
Shipping Dimensions (HWD/cm)	4.50 x 8.99 x 27.00
Shipping weight (lbs)	.90
Shipping weight (kg)	0.41
Unit Dimensions (HWD/in)	1.20 x 1.70 x 9.45
Unit Dimensions (HWD/cm)	3.05 x 4.32 x 24.01
Unit weight (lbs)	.77
Unit weight (kg)	0.35
Material of construction	Plastic
Integrated keyhole mounting tabs	Keyhole mounting tabs enable mounting to a variety of surfaces
Style	Strip
CERTIFICATIONS	
UL1363 (Power Tap)	UL1363
cUL / CSA (Canada)	cUL

**WARRANTY****Product Warranty Period  
(Worldwide)**

Lifetime limited warranty

More information, including related products, owner's manuals, and additional technical specifications, can be found online at [www.tripplite.com/en/products/model.cfm?txtModelID=1966](http://www.tripplite.com/en/products/model.cfm?txtModelID=1966).

---

Copyright © 2013 Tripp Lite. All rights reserved. All trademarks are the sole property of their respective owners. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Photos may differ slightly from final products.