



**Tripp Lite**  
1111 West 35th Street  
Chicago, IL 60609 USA  
Telephone: +(773) 869 1234  
E-mail: [saleshelp@tripplite.com](mailto:saleshelp@tripplite.com)

## Model #: SUPER6TEL12

### 7 outlet, 12ft cord, 1080 joules, Modem/Fax Protection - Protect It! Surge Suppressor



#### Highlights

- 7 outlets / 12-ft. cord
- 1080 joule rating
- Modem/fax surge protection
- \$50,000 [Ultimate Lifetime Insurance](#) (USA, Puerto Rico & Canada only)

#### Description

Tripp Lite's SUPER6TEL12 surge suppressor offers complete AC and phone line surge suppression for comprehensive protection of workstations, desktop PCs, telecom systems and other sensitive electronics. High-grade AC surge suppression shields connected equipment from damage and performance problems due to transient surges. Set of RJ11 telephone line suppression jacks protect dialup and DSL modem lines, fax machines, cordless phones and more. SUPER6TEL12 offers 7 total outlets, 12 foot cord with a space-saving right-angle plug and diagnostic LEDs to warn of wiring problems and suppressor damage. Heavy grade AC suppression rated at 1080 joules shields equipment from surges and line noise. Attractive white suppressor housing with keyhole mounting tabs and 3 designated transformer plug outlets offers convenient protection of desktop computer equipment and accessories. \$50,000 [Ultimate Lifetime Insurance](#) (USA and Canada Only). PLUG/OUTLETS: Input: NEMA5-15P/Output: 7 NEMA5-15R/12-ft. AC line cord ELECTRICAL: 120V AC, 50/60Hz, 15A (Requires NEMA5-15R wall receptacle) FORMAT: Corded multi-outlet strip with 3 transformer spaced outlets SUPPRESSION: AC: 150V RMS Clamping/1080 joules/330V UL1449 Let-through Rating Phone: Single telephone line surge suppression (RJ11 jacks, 2 wire, 1 line)

#### Package Includes

- SUPER6TEL12 Surge Suppressor
- 6-ft. telephone cord
- Instruction manual with warranty information

#### Features

- 1080 joules AC surge suppression shields equipment from the strongest surges and line noise
- 7 AC outlets with room for 3 transformer plugs without blocking outlets covers computers and all peripherals
- Phone line surge suppression protects both dialup and DSL modems, plus fax machines, cordless phones and more (pair of RJ11 jacks, 2 wire, 1 line, includes 6 ft phone cable)
- 12 foot cord with a space-saving right angle plug
- Built-in power switch and 15 amp circuit breaker offers power control and overload protection over all outlets
- Fail-safe thermal fusing protects against fire and other damage in the event of an extreme, extended overvoltage or surge condition
- Diagnostic LEDs confirm outlet grounding and surge suppression status
- Attractive white suppressor housing with keyhole mounting tabs allow versatile placement options
- UL1449 3rd Edition Rated (330V all modes), UL1363 (Power Tap), UL497A (Communications), Meets FCC part 68 rules, cUL (Canada)
- Exceeds IEEE 587 category A & B surge suppression specifications
- \$50,000 Ultimate Lifetime [connected equipment insurance](#) (USA and Canada Only)

#### Specifications

##### OVERVIEW

Intended Application	Home/Office
<b>OUTPUT</b>	
Frequency compatibility	50 / 60 Hz
Output watts	1800
Circuit Breaker (amps)	15
Outlet quantity / type	7 NEMA 5-15R
Transformer accommodation	Supports 3 large transformer plug accessories without covering remaining outlets, accepts up to 5 transformers total
Outlet orientation	Single row of 5, plus 2 side mounted outlets
<b>INPUT</b>	
Nominal Input Voltage(s) Supported	120V AC
Recommended Electrical Service	120V (110-125V)
Input connection type	NEMA 5-15P
Input cord length (ft.)	12
Input cord length (m)	3.7
Input cord gauge, type	14 gauge, SJT
Voltage compatibility (VAC)	120
Maximum Surge Amps	72000
<b>LEDS ALARMS &amp; SWITCHES</b>	
Switches	Two position on/off power switch
Diagnostic LEDs	Built-in LED confirms suppressor "protection present" (green) status
<b>SURGE / NOISE SUPPRESSION</b>	
AC suppression joule rating	1080
AC suppression response time	< 1 ns
Protection modes	Includes full normal mode (H-N) and common mode (N-G / H-G) line surge suppression
Clamping voltage (RMS)	150V
UL1449 let through rating	330V - UL Verified
EMI / RFI filtering	Up to 20 dB
<b>DATALINE SURGE SUPPRESSION</b>	
Telephone/DSL Protection	Yes
Telephone/DSL Protection Details	1 line
Cable (Coax) Protection	No
Network (Ethernet) Protection	No
<b>PHYSICAL</b>	

Shipping Dimensions (HWD/in)	12.4 x 7.09 x 1.77
Shipping Dimensions (HWD/cm)	31.50 x 18.01 x 4.50
Shipping weight (lbs)	1.98
Shipping weight (kg)	0.90
Unit Dimensions (HWD/in)	1.54 x 2.72 x 10.3
Unit Dimensions (HWD/cm)	3.91 x 6.91 x 26.16
Unit weight (lbs)	1.82
Unit weight (kg)	0.83
Material of construction	Plastic
Integrated keyhole mounting tabs	Keyhole mounting tabs enable wall mounting
Housing Color	Light Gray
Receptacle Color	Light Gray
AC line cord color	Light Gray
Style	Strip
Outlets center to center measurement	Between Standard Outlets = 29mm; Between Transformer Outlets = 48mm
Keyhole slot center to center measurement	Distance between slots = 78mm; Distance between slot height = 24mm
<b>SPECIAL FEATURES</b>	
Right-Angle Plug	Yes
<b>CERTIFICATIONS</b>	
UL1449 3rd Edition (AC Suppression)	UL1449 3rd Edition
UL1363 (Power Tap)	UL1363
UL497A (Communications)	UL497A
FCC Part 68 (Communications)	FCC Part 68
cUL / CSA (Canada)	cUL
Industry Canada (Communications)	Industry Canada
Approvals	Exceeds IEEE 587 category A&B specifications
<b>WARRANTY</b>	
Product Warranty Period (Worldwide)	Lifetime limited warranty
Connected Equipment Insurance (U.S., Canada & Puerto Rico)	\$50,000 <a href="#">Ultimate Lifetime Insurance</a>

---

More information, including related products, owner's manuals, and additional technical specifications, can be found online at [www.tripplite.com/en/products/model.cfm?txtModelID=136](http://www.tripplite.com/en/products/model.cfm?txtModelID=136).

---

Copyright © 2013 Tripp Lite. All rights reserved. All trademarks are the sole property of their respective owners. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Photos may differ slightly from final products.