


Edge profiles



Combination profiles

KO H 0 	M 13 M 46	KO H 1 	M 13 M 46	KO H 2 	M 13 M 46	KO H 4A 	M 13 M 46	KO H 6 	M 14 M 46	KO H 7 	M 14
KO H 8 	M 14 M 46	KO H 10 	M 14 M 46	KO H 14 	M 14 M 46	KOP 2 	M 13	KOE 14 	M 14	KOE 2 	M 13
KOT 2 	M 13	KON 2 	M 13	KOK 14 	M 15	KOL 1 	M 15	KOL 2 	M 15	KOW 2 	M 15
KOK 2 	M 13	KO HL 0 	M 16	KO HL 1 	M 16	KO HL 2 	M 16	KO HL 4 	M 16	KO HL 6 	M 16
KO HL 10 	M 16	KO HL 14 	M 17	KOLL 2 	M 17	KOTL 2 	M 17	KOR 2 	M 13	KOG 5 	M 14
KOF 3 	M 14										

Tube profiles

TUG 03 M 23 	TUG 05 M 23 M 47 	TUG 09 M 23 	TUG 17 M 23 M 47 	GP 211 M 20 	GB 50 M 19
GP 213 M 21 M 43 	GP 217 M 21 M 43 	GP 214 M 21 M 43 	GP 216 M 22 M 43 	GP 215 M 22 M 43 	GP 218 M 21 M 43
GP 219 M 21 M 43 	GP 220 M 21 M 43 	GB 87 M 25 M 42 	GB 88 M 25 M 42 	TUG V 09 M 24 	TUG V 17 M 24








Profiles for cases with slide-in cover panel

GB 81 M 6 	GB 82 M 6 	GB 83 M 6 	GB 84 M 6
---------------	---------------	---------------	---------------












Profiles for design case „Frame“ with integrated heatsink

GB 89 M 44 	GB 90 M 44 	GB 91 M 44
----------------	----------------	----------------



Side panel profiles

GB 36  M 9	GB 38  M 9	GB 76  M 7 M 45	GB 77  M 7 M 45	GB 78  M 7 M 45	GB 79  M 7 M 45
G 118  M 35					







Profiles for subracks

GB 29  N 15 N 30 N 74	GB 30  N 15 N 30 N 74	GB 31  N 74	GB 32  N 74	GB 33  N 74	GB 34  N 74
GB 5  N 74	GB 20  N 74	GB 27  N 75	GB 35  N 15 N 73	GB 37  N 75	

Profiles for part front panels

GL 7  N 60 N 76	GB 14  N 76
---	--


Profiles for 19" plug-in boxes

GB 18  N 6 N 71	GB 19  N 6 N 71	GB 21  N 71	GB 22  N 8 N 71	GB 23  N 8 N 10 N 71	GB 52  M 4
---	---	--	---	---	---

Profiles for 19" front panels

<p>GB 28 N 7 N 10 N 72</p>	<p>GB 40 N 7 N 72</p>	<p>GB 41 N 7 N 72</p>	<p>GB 54 N 7 N 72</p>	<p>GB 55 N 7 N 72</p>
------------------------------------	---------------------------	---------------------------	---------------------------	---------------------------















Profiles for mechanical engineering



Profiles for case with cooling fins

<p>GB 56 M 32</p>	<p>KRH 6 M 36</p>	<p>KOS 5 M 36</p>	<p>GB 53 M 37 N 73</p>	<p>SK 61 M 34</p>
<p>SK LED 1 M 38</p>	<p>SK LED 2 M 38</p>	<p>SK LED 3 M 38</p>		

Profiles for insert modules

<p>GP 190 N 39 N 77</p> 	<p>GP 191 N 36 N 77</p> 	<p>GP 192 N 36 N 37 N 77</p> 	<p>GP 193 N 37 N 38 N 77</p> 	<p>GP 195 N 41 N 42 N 80</p> 	<p>GP 196 N 41 N 80</p> 
<p>GP 197 N 42 N 43 N 80</p> 	<p>GP 199 N 48 N 76</p> 	<p>GP 200 N 38 N 78</p> 	<p>GP 201 N 38 N 78</p> 	<p>GP 202 N 38 N 78</p> 	<p>GP 206 N 40 N 79</p> 
<p>GP 207 N 40 N 79</p> 	<p>GP 208 N 40 N 79</p> 	<p>GP 209 N 40 N 79</p> 