

19" CABINETS

CamRack-LX

Quick Assembly **5 minutes!**

19" Modular cabinets, 600mm wide, designed for cabling, telecommunications, IT and industrial and home installations

- Aluminium profile external structure with diecast high resistance corners.
- 4x19" sections adjustable in depths (gaps of 20mm). Manufactured in steel 2/1,5 mm.
- Front door in safety glass, frame with springswivel hinge and opening angle 190°
- Removable side panels with ¼ turn locks.
- Steel rear door with lock.
- ¼ -turn locking ventilated top panels with cable entries.
- 4 adjustable levelling feet.
- Distributed load capacity: 1.000 Kg (static) / 300 Kg (dynamic)
- Finishes: RAL 7016, Dark grey, anthracite (See below for corner options)




Glass Front Door

PART NO.	U	WIDTH	DEPTH
CLX126602	12	600mm	600mm
CLX186602	18	600mm	600mm
CLX246602	24	600mm	600mm
CLX306602	30	600mm	600mm
CLX366602	36	600mm	600mm
CLX366802	36	600mm	800mm
CLX426602	42	600mm	600mm
CLX426802	42	600mm	800mm
CLX428602	42	800mm	600mm
CLX428802	42	800mm	800mm

No Front Door

PART NO.	U	WIDTH	DEPTH
CLX126612	12	600mm	600mm
CLX186612	18	600mm	600mm
CLX246612	24	600mm	600mm
CLX306612	30	600mm	600mm
CLX366612	36	600mm	600mm
CLX366812	36	600mm	800mm
CLX426612	42	600mm	600mm
CLX426812	42	600mm	800mm
CLX428602	42	800mm	600mm
CLX428812	42	800mm	800mm

- **Standard corner colours:**



White

Red

Blue

Orange

Black

- **Other corner colours available upon request:**



Yellow

Green

Purple

Lilac

Grey