

## General Information

Extended Product Type:	M4/6.P
Product ID:	1SNA165113R1600
EAN:	3472591651133
Catalog Description:	M4/6.P
Long Description:	M4/6.P Screw Clamp Terminal Blocks Ground

## Categories

Products » Low Voltage Products and Systems » Connection Devices » Terminal Blocks » Screw Clamp Terminal Blocks

## Ordering

EAN:	3472591651133
Minimum Order Quantity:	50 piece
Customs Tariff Number:	85369010

## Dimensions

Product Net Width:	6.0 mm
Product Net Weight:	0.021 kg

## Container Information

Package Level 1 Units:	50 piece
Package Level 1 Width:	61 mm
Package Level 1 Height:	47 mm
Package Level 1 Length:	220 mm
Package Level 1 Gross Weight:	1.050 kg
Package Level 1 EAN:	3472591651133
Package Level 2 Units:	1000 piece
Package Level 2 Width:	300 mm
Package Level 2 Height:	150 mm
Package Level 2 Length:	500 mm
Package Level 2 Gross Weight:	21.350 kg
Package Level 3 Units:	48000 piece
Product Packing Type:	Box

## Environmental

RoHS Status:	Following EU Directive 2002/95/EC August 18, 2005 and amendment
--------------	---

## Technical UL/CSA

Connecting Capacity-Main Circuit UL/CSA:	Screw Clamp / Rigid 1x 22-12 AWG
Connecting Capacity UL/CSA:	Screw Clamp / Rigid 22-12 AWG
Flammability According to UL94:	V0

## Additional Information

Color:	Green-Yellow
Connecting Capacity-Main Circuit:	Screw Clamp / Flexible 1x 0.22-4 mm <sup>2</sup> Screw Clamp / Rigid 1x 0.2-4 mm <sup>2</sup> Screw Clamp / With Insulated Ferrule 1x 2.5 mm <sup>2</sup>
Connection Type:	Screw clamp
Function:	Ground
Gauge Type:	A4
IIT Publishing Status:	Level 0 - Information enabled
Mounting on DIN Rail:	G32 (32 x 15 mm Mounting Rail) acc. to IEC 60715 TH35-7.5 (35 x 7.5 mm Mounting Rail) acc. to IEC 60715 TH35-15 (35 x 15 mm Mounting Rail) acc. to IEC 60715
Pollution Degree:	3
Product Main Type:	M4/6.P
Product Name:	Terminal block
Rated Cross-Section:	4 mm <sup>2</sup>
Rated Short-time Withstand Current (I <sub>cw</sub> ):	for 1.0s 480 A
Recommended Screw Driver:	4
RoHS Date:	20050818
Spacing:	6 mm
Sub-Function:	2 connections

<b>Sub-Function 2:</b>	Screw rail connection
<b>Tightening Torques:</b>	acc. IEC 60947-1 0.5 N·m Manufacturer 0.8 N·m
<b>Wire Stripping Length:</b>	9.5 mm

### Certificates and Declarations (Document Number)

<b>CSA Certificate:</b>	<a href="#">TBD - OK in Ag.Base</a>
<b>cUL Certificate:</b>	<a href="#">1SND161011A0202</a>
<b>Declaration of Conformity - CE:</b>	<a href="#">1SND225004C1000</a>
<b>GOST Certificate:</b>	<a href="#">1SND161005A1103</a>

### Classifications

<b>E-nummer:</b>	2925525
<b>Object Classification Code:</b>	X

