
Item no.: 281-101
Product description: 2-CONDUCTOR THROUGH TERMINAL BLOCK



Produkt kann von Bild abweichen / product may differ

Packing unit 100 pieces

RoHS compliant

Product group	1 (Rail Mounted Terminal Blocks)
Cross section [mm ²]	0.08 - 4 mm ²
Cross section [AWG]	28 - 12 AWG
Connection method	CAGE CLAMP® CONNECTION
Measured voltage EN	800 V
Measured shock voltage	8 kV
Pollution degree	3
Current intensity EN	32 A
Weight	5.934 g
Color	gray
Wiring type	Side-entry
No. of connection Points	2
No. of potentials	1
Height	32.5 mm
Height	1.28 in
Width	6 mm
Width	0.236 in
Depth	42.5 mm
Depth	1.67 in

Strip length from	9 mm
Strip length to	10 mm
Strip length	0.37 in
Mounting	TS 35



Item no.	Admission office	Approval no.	Voltage [V]	Current [A]	Cross section [mm ²]
281-101	ABS	05-HG476175/3-PDA	800	32	4,0
281-101	BV	07436/Co	800	32	4,0
281-101	CCA	NL5591/1	800		4
281-101	CSA	154112-1505034	600	25	28-12
281-101	DNV	E-10423	800	32	4,0
281-101	GL	17295-00HH	800	32	4
281-101	KEMA	2076376.01	800		4
281-101	KR	HMB05880-EL001	500/800	10/35	4
281-101	LR	91/20112(E6)	800	32	4,0
281-101	PRS	TE/1718/880590/08	800		4
281-101	PTB	PTB00Atex3110U	550	28	4
281-101	RMR	11130002	800	32	4,0
281-101	RosTest	8189158	550	28	4
281-101	UR	E45172	600	20	28-12

Sorting criteria: admission office - approval number

© WAGO Kontakttechnik GmbH & Co. KG

Specifications are subject to changes and errors may be expected