



e970Swn

47cm (18.5") LED MONITOR

Line:

Line:	Value
Paneltype:	WLED
Monitor Size:	18.5"
Visible Screen Size:	47cm
Screen Format:	16:9
Brightness:	200 (typ) cd/m ²
Contrast Ratio Dynamic:	20.000.000:1
Contrast Ratio Typical:	700:1
Pixel / Dot / Pitch:	0.3 (H) x 0.3 (V)
Display Area:	410 (H) x 230 (V)
Viewing Angle:	90°/65° (CR 10)
Response Time:	5 ms

Scanning Frequency:

Scanning Frequency:	H: 30-60 KHz / V: 50-76 HZ
Pixel Frequency:	85.5 MHz

Resolution:

Maximum Resolution:	1366 x 768@60Hz
Recommend Resolution:	1366 x 768@60Hz
Colors:	16.7 M
HDCP compatible:	No

Signal Input:


Analogue Input: D-Sub:	Yes
Digital Input: DVI-D / HDMI:	No / No
Composite CVBS Input:	No
Component CVBS Input:	No
S-Video Input:	No
Component Input:	No
SCART:	No
CI Card:	No
Display Port Input:	No

Connectors:

D-Sub 15 pin:	Yes
DVI-D 24-pin:	No
HDMI:	No
Display Port Input:	No

Power:

Power Source:	On: 15W; Standby: 0.5W; Off: 0.5W
Power Consumption:	90 ~ 240 VAC, 50 / 60 Hz





e970Swn

47cm (18.5") LED MONITOR

Tuner System:

-

Other Features:

User Control:	Button
Speaker:	No
Wallmount:	Yes
Height adjustment:	No
Pivot:	No
Swivel:	No

Regulations:	CE Energy Star 6 EPEAT Gold EuP ISO 9241-307 FCC GOST NRTL RoHS TÜV-GS
--------------	---

Other Features:	-3/10 Tilt Eco Mode e-Saver i-Menu Screen+ Kensington Security Lock VESA 100 mm
-----------------	---

Accessoires:

Accessoires:	Power cable D-Sub cable Driver CD Warranty Card on CD-ROM
--------------	--

Dimensions:

Dimensions (WxHxD):	437.4 x 271.6 x 47.7 mm
Weight:	2.15 kg w/o packaging // 2.8 kg w/ packaging
Warranty:	3 Years
EAN:	4038986193788

