


FMC 0,5/ 3-ST-2,54


Order No.: 1821106

The figure shows a 10-position version of the product

<http://eshop.phoenixcontact.co.uk/phoenix/treeViewClick.do?UID=1821106>

Plug component, Nominal current: 6 A, Rated voltage (III/2): 160 V,
Number of positions: 3, Pitch: 2.54 mm, Connection method: Spring-
cage conn., Color: Black, Contact surface: Gold

Commercial data

EAN	 4 046356 789165
Note	Made-to-order
Pack	200
Customs tariff	85366990
Gross weight in pieces	0.84 g
Country of Origin	DE
Catalog page information	Page 174 (CAT-1-2013)

Product notes

WEEE/RoHS-compliant since:
30/07/2012



Please note that the data given here has been taken from the online catalog. For comprehensive information and data, please refer to the user documentation at <http://www.download.phoenixcontact.com>. The General Terms and Conditions of Use apply to Internet downloads.

Certificates

Certification

Certifications applied for:

Certification Ex:

Accessories


Item	Designation	Description
General		
3202478	A 0,25- 7	Ferrule, Length: 7 mm, Color: silver
3009202	A 0,34- 7	Ferrule, Length: 7 mm, Color: silver
Marking		
0804853	SK 2,54/2,8:FORTL.ZAHLEN	Marker cards, Card, white, labeled, Horizontal: Consecutive numbers 1 - 10, 11 - 20, etc. up to 91 - 99, Mounting type: Adhesive, For terminal block width: 2.54 mm
Tools		
1212034	CRIMPFOX 6	Crimping pliers, for ferrules as per DIN 46228 section 1+4, 0.25 - 6.0 mm ² , insertion from the side, trapezoidal crimp
1205202	SZS 0,4X2,0	Micro screwdriver, bladed, size: 0.4 x 2.0 x 60 mm, 2-component grip, with non-slip grip and twist cap

Additional products

Item	Designation	Description
General		
1821258	MC 0,5/ 3-G-2,54 P20 THR R24	Header, Nominal current: 6 A, Rated voltage (III/2): 160 V, Number of positions: 3, Pitch: 2.54 mm, Color: Black, Contact surface: Gold, Assembly: Taped SMD/THT/THR components
1821708	MC 0,5/ 3-G-2,54 SMD R24	Header, Nominal current: 6 A, Rated voltage (III/2): 160 V, Number of positions: 3, Pitch: 2.54 mm, Color: Black, Contact surface: Gold, Assembly: Taped SMD/THT/THR components
1821407	MCV 0,5/ 3-G-2,54 P20 THR R24	Header, Nominal current: 6 A, Rated voltage (III/2): 160 V, Number of positions: 3, Pitch: 2.54 mm, Color: Black, Contact surface: Gold, Assembly: Taped SMD/THT/THR components
1821559	MCV 0,5/ 3-G-2,54 SMD R24	Header, Nominal current: 6 A, Rated voltage (III/2): 160 V, Number of positions: 3, Pitch: 2.54 mm, Color: Black, Contact surface: Gold, Assembly: Taped SMD/THT/THR components

Drawings

Dimensioned drawing



Address

PHOENIX CONTACT Ltd
Halesfield 13
Telford / Shropshire / TF7 4PG,England
Phone 01952 681 700
Fax 01952 681 799
<http://www.phoenixcontact.co.uk>



Phoenix Contact Ltd.
Technical modifications reserved;