


## FMC 0,5/ 4-ST-2,54


Order No.: 1821119

The figure shows a 10-position version of the product

<http://eshop.phoenixcontact.co.uk/phoenix/treeViewClick.do?UID=1821119>

Plug component, Nominal current: 6 A, Rated voltage (III/2): 160 V,  
Number of positions: 4, Pitch: 2.54 mm, Connection method: Spring-  
cage conn., Color: Black, Contact surface: Gold

### Commercial data

EAN	 4 046356 789271
Note	Made-to-order
Pack	200
Customs tariff	85366990
Gross weight in pieces	1.08 g
Country of Origin	DE
Catalog page information	Page 174 (CAT-1-2013)

### Product notes

WEEE/RoHS-compliant since:  
30/07/2012



Please note that the data given here has been taken from the online catalog. For comprehensive information and data, please refer to the user documentation at <http://www.download.phoenixcontact.com>. The General Terms and Conditions of Use apply to Internet downloads.

### Certificates

Certification

Certifications applied for:

Certification Ex:

### Accessories

Item	Designation	Description
<b>General</b>		
3202478	A 0,25- 7	Ferrule, Length: 7 mm, Color: silver
3009202	A 0,34- 7	Ferrule, Length: 7 mm, Color: silver
<b>Marking</b>		
0804853	SK 2,54/2,8:FORTL.ZAHLEN	Marker cards, Card, white, labeled, Horizontal: Consecutive numbers 1 - 10, 11 - 20, etc. up to 91 - 99, Mounting type: Adhesive, For terminal block width: 2.54 mm
<b>Tools</b>		
1212034	CRIMPFOX 6	Crimping pliers, for ferrules as per DIN 46228 section 1+4, 0.25 - 6.0 mm <sup>2</sup> , insertion from the side, trapezoidal crimp
1205202	SZS 0,4X2,0	Micro screwdriver, bladed, size: 0.4 x 2.0 x 60 mm, 2-component grip, with non-slip grip and twist cap


### Additional products

Item	Designation	Description
<b>General</b>		
1821261	MC 0,5/ 4-G-2,54 P20 THR R24	Header, Nominal current: 6 A, Rated voltage (III/2): 160 V, Number of positions: 4, Pitch: 2.54 mm, Color: Black, Contact surface: Gold, Assembly: Taped SMD/THT/THR components
1821711	MC 0,5/ 4-G-2,54 SMD R24	Header, Nominal current: 6 A, Rated voltage (III/2): 160 V, Number of positions: 4, Pitch: 2.54 mm, Color: Black, Contact surface: Gold, Assembly: Taped SMD/THT/THR components
1821410	MCV 0,5/ 4-G-2,54 P20 THR R24	Header, Nominal current: 6 A, Rated voltage (III/2): 160 V, Number of positions: 4, Pitch: 2.54 mm, Color: Black, Contact surface: Gold, Assembly: Taped SMD/THT/THR components
1821562	MCV 0,5/ 4-G-2,54 SMD R24	Header, Nominal current: 6 A, Rated voltage (III/2): 160 V, Number of positions: 4, Pitch: 2.54 mm, Color: Black, Contact surface: Gold, Assembly: Taped SMD/THT/THR components

## Drawings

### Dimensioned drawing

---



**Address**

PHOENIX CONTACT Ltd  
Halesfield 13  
Telford / Shropshire / TF7 4PG,England  
Phone 01952 681 700  
Fax 01952 681 799  
<http://www.phoenixcontact.co.uk>



Phoenix Contact Ltd.  
Technical modifications reserved;