













Kraftform Kompakt SH1 Plumbing / Heating / Plumbkit



2 jokers Ratchet wrench with holding function for screw and nut, with end stop to prevent slipping down , with double hexagonal geometry and extremely hard coatings on the metal plate against slippage at high torque , with small return angle of 30 ° , 1 Cyclops ratchet 8000 A (1/4 ") for fast and powerful operation ; 3 Cyclops nuts 8790 HMA for hand and machine use ; 1 Cyclops adapter 8784 A1 for bits; 6 TORX ® HF bits 867/4 with holding function for TORX ® screws for secure out without losing the screws , 1 voltage tester 247; 2 Kraftform 100 Series VDE screwdriver 160 i and 160 iS for safe working up to 1,000 volts (160 iS with reduced blade diameter with integrated protective insulation for the reach and operate in low-lying fastening and spring elements); 1 Kraftform Chiseldriver 932 A (slot) with continuous hexagon blade and integrated impact cap for screw and chiselling , 2 socket wrench screwdriver 395 HO with hollow shaft for tightening or loosening of screws on long bolts and of stubborn screws .



Code

05135927001	Joker	1 x 10x159; 1 x 13x177
	 8000 A	1 x 1/4"x152,0
	 8790 HMA	1 x 7,0x23,0; 1 x 10,0x23,0; 1 x 13,0x23,0
	  8784 A1	1 x 1/4"x1/4"x37,0
	 867/4 TORX® HF	1 x TX 10x50; 1 x TX 15x50; 1 x TX 20x50; 1 x TX 25x50; 1 x TX 30x50; 1 x TX 40x50
	 851/4 Z PH	1 x PH 1x89; 1 x PH 2x89
	 840/4 Z Hex-Plus	1 x 3,0x89; 1 x 4,0x89; 1 x 5,0x89; 1 x 6,0x89
	 247	1 x 0,5x3,0x70
	 160 iS	1 x 0,6x3,5x100
	 160 i VDE	1 x 1,0x5,5x125
	 932 A	1 x 1,2x7,0x125
	 395 HO	1 x 10,0x80; 1 x 13,0x80