


- Replacement for 10W halogen bulbs
- Up to 90% energy saving
- Lifetime of 25,000 hrs
- Suitable replacement for bi-pin lamps used for accent lighting, vanity and cabinet lighting.



Order Code	52143
General Data	
Lamp Socket	G4 Bi Pin
Design	Capsule
Geometric Data	
Length (mm)	41
Diameter (mm)	13.8
Weight (g)	8
Electric Data	
Wattage (W)	1
Wattage Equivalent (W)	10
Voltage (V)	12V DC/AC
Power Factor	-
Operating Frequency (Hz)	50-60
Photometric Data	
Luminous Flux (lm)	80
Luminous Flux 90° cone (lm)	n/a
CRI	≥ 80
CCT (K)	2700
Luminous Intensity (cd)	27
Beam Angle (°)	100
Lifespan	
Lifetime (hrs)	25,000
Switching Cycle	40,000
Dimmability	
	No
Energy Efficiency Class	
	A++



ø13.8mm





Order Code	52143
Product Description	LED BI PIN G4 Capsule 1.0W 12V AC/DC 2700K WW 80LM

Technical Packaging Details

Barcode	023942521433
EAN 128	(02)00023942521433(37)10(91)14
EAN 14	50023942521438
Pack Dimensions (HxWxL)	
Pack Weight	TBC
Carton Qty (Shipping Unit)	10
Carton Dimensions (HxWxL)	145*95*155
Cartons/Pallet	276
Layers/Pallet	6
Units/Pallet	2760

Photometric Diagram

52143

