



- Replacement for incandescent 26 W
- Up to 87% energy saving
- Lifetime of 30,000 hrs
- An energy efficient LED solution for general lighting.



Order Code	52126
<b>General Data</b>	
Lamp Socket	E27
Design	Frosted
<b>Geometric Data</b>	
Length (mm)	112
Diameter (mm)	60
Weight (g)	155
<b>Electric Data</b>	
Wattage (W)	3.5
Voltage (V)	220-240
Power Factor	≥ 0.40
Operating Frequency (Hz)	50-60
<b>Photometric Data</b>	
Luminous Flux (lm)	270
CRI	≥ 80
CCT (K)	3000
Luminous Intensity (cd)	-
Beam Angle (°)	130
Lifetime (hrs)	30,000
<b>Switching Cycle</b>	20,000
<b>Wattage Equivalent (W)</b>	26
<b>Energy Efficiency Class</b>	A+





<b>Order Code</b>	52126
<b>Product Description</b>	LED Classic A E27 3.5W 3000K WW 270LM 130DEG

**Technical Packaging Details**

Barcode	023942521266
EAN 128	(02)00023942521266(37)04(91)204
EAN 14	50023942521261
Pack Dimensions (HxWxL)	178 mm x 118 mm x 61 mm
Pack Weight	TBC
Carton Qty (Shipping Unit)	4
Carton Dimensions (HxWxL)	195 mm x 144 mm x 253 mm
Cartons/Pallet	80
Layers/Pallet	4
Units/Pallet	320

## Photometric Diagram

52126

