

- Replacement for incandescent 41 W
- Up to 84% energy saving
- Lifetime of 30,000 hrs
- An energy efficient LED solution for general lighting.



Order Code 52130

General Data

Lamp Socket E27

Design Frosted

Geometric Data

Length (mm) 112

Diameter (mm) 60

Weight (g) 155

Electric Data

Wattage (W) 6.5

Voltage (V) 220-240

Power Factor ≥ 0.85

Operating Frequency (Hz) 50-60

Photometric Data

Luminous Flux (lm) 480

CRI ≥ 80

CCT (K) 3000

Luminous Intensity (cd) -


Beam Angle ($^{\circ}$) 130


Lifetime (hrs) 30,000

Switching Cycle 20,000

Wattage Equivalent (W) 41

Energy Efficiency Class A+





Order Code	52130
Product Description	LED Classic A E27 6.5W 3000K WW 480LM 130DEG

Technical Packaging Details

Barcode	023942521303
EAN 128	(02)00023942521303(37)04(91)204
EAN 14	50023942521308
Pack Dimensions (HxWxL)	178 mm x 118 mm x 61 mm
Pack Weight	TBC
Carton Qty (Shipping Unit)	4
Carton Dimensions (HxWxL)	195 mm x 144 mm x 253 mm
Cartons/Pallet	80
Layers/Pallet	4
Units/Pallet	320

Photometric Diagram

52130

