

- Replacement for 27W PAR16 halogen lamp
- Up to 85% energy saving
- Lifetime of 30,000 hrs
- Suitable replacement for halogen or incandescent spots. Perfectly highlights the corridors, stairwells, bathroom etc at home and in hospitality areas.



Order Code 52139

General Data

Lamp Socket E14
Design Lens

Geometric Data

Length (mm) 76
Diameter (mm) 50
Weight (g) 63

Electric Data

Wattage (W) 4.0
Wattage Equivalent (W) 27
Voltage (V) 220-240
Power Factor >0.40
Operating Frequency (Hz) 50-60

Photometric Data


Luminous Flux (lm) 200
Luminous Flux 90° (lm) 160
CRI ≥ 80
CCT (K) 3000
Luminous Intensity (cd) 750
Beam Angle (°) 20


Lifespan

Lifetime (hrs) 30,000
Switching Cycle 20,000

Dimmability No

Energy Efficiency Class A






Order Code	52139
Product Description	LED PAR16 E14 4.0W 3000K WW 160LM 20DEG

Technical Packaging Details

Barcode	023942521396
EAN 128	(02)00023942521396(37)04(91)204
EAN 14	50023942521391
Pack Dimensions (HxWxL)	192 mm x 118 mm x 61 mm
Pack Weight	TBC
Carton Qty (Shipping Unit)	4
Carton Dimensions (HxWxL)	192mm x 118mm x 250mm
Cartons/Pallet	104
Layers/Pallet	4
Units/Pallet	416

Photometric Diagram

52139



Distance [m]	Cone Diameter [m]	E(0°)	E(C90)	E(C0)	Illuminance [lx]
0.5	0.17 0.27	3307	1596	1546	
1.0	0.33 0.54	827	399	386	
1.5	0.50 0.81	367	177	172	
2.0	0.67 1.08	207	100	97	
2.5	0.84 1.35	132	64	62	
3.0	1.00 1.62	92	44	43	

Distance [m] Cone Diameter [m] Illuminance [lx]

— C0 - C180 (Half-value Angle: 30.2°)
— C90 - C270 (Half-value Angle: 19.0°)