

- Replacement for 25 W E14 candle lamp
- 85% energy saving
- Lifetime of 30,000 hrs
- Ideal for general and decorative lighting at home and in hospitality environments. This candle lamp enhances the appeal of the chandelier and other luminaires both when lit up and when not.



Order Code 52136

General Data

Lamp Socket E14
Design Frost

Geometric Data

Length (mm) 102
Diameter (mm) 38
Weight (g) 40

Electric Data

Wattage (W) 3.8
Voltage (V) 220-240
Power Factor ≥ 0.40
Operating Frequency (Hz) 50-60


Photometric Data


Luminous Flux (lm) 250
CRI ≥ 80
CCT (K) 2700
Luminous Intensity (cd) -
Beam Angle (°) -
Lifetime (hrs) 30,000

Switching cycle 20,000

Wattage Equivalent (W) 25

Energy Efficiency Class A+





Order Code	52136
Product Description	LED CLASSIC B 3.8W 2700K WW 250LM Blister

Technical Packaging Details

Barcode	023942521365
EAN 128	(02)00023942521365(37)04(91)204
EAN 14	50023942521360
Pack Dimensions (HxWxL)	178 mm x 118 mm x 45 mm
Pack Weight	TBC
Carton Qty (Shipping Unit)	4
Carton Dimensions (HxWxL)	192 mm x 92 mm x 252 mm
Cartons/Layer	140
Layers/Pallet	5
Units/Pallet	560

Photometric Diagram

52136

