

- Excellent replacement for 25W incandescent lamp
- 86% energy saving
- Long lifetime of 30,000 hours
- Ideal energy efficient LED solution for general lighting at home, in hotel rooms, restaurants or other similar applications where 25W lamps are used.



Order Code 52134

General Data

Lamp Socket E14

Design Clear

Geometric Data

Length (mm) 78

Diameter (mm) 45

Weight (g) 52

Electric Data

Wattage (W) 3.5

Voltage (V) 220-240

Power Factor ≥ 0.40

Operating Frequency (Hz) 50-60

Photometric Data

Luminous Flux (lm) 250

CRI ≥ 80

CCT (K) 3000

Luminous Intensity (cd) -

Beam Angle (°) -


Lifetime (hrs) 30,000

Switching cycle 20,000

Wattage Equivalent (W) 25

Energy Efficiency Class A+





| | |
|----------------------------|---|
| Order Code | 52134 |
| Product Description | LED Mini Globe E14 3.5W 3000K WW 250LM 160DEG |

Technical Packaging Details

| | |
|----------------------------|---------------------------------|
| Barcode | 023942521341 |
| EAN 128 | (02)00023942521341(37)04(91)204 |
| EAN 14 | 50023942521346 |
| Pack Dimensions (HxWxL) | 145 mm x 103 mm x 51 mm |
| Pack Weight | 74 g |
| Carton Qty (Shipping Unit) | 4 |
| Carton Dimensions (HxWxL) | 160 mm x 117 mm x 223 mm |
| Cartons/Pallet | 150 |
| Layers/Pallet | 5 |
| Units/Pallet | 600 |

Photometric Diagram

52134

