



LFM LED Magnifiers

The LFM LED Magnifier is Luxo's most cost-effective addition to its growing line of LED Magnifiers. 9.5W dimmable LEDs (with a total power consumption of 10W) with a 4000°K color temperature guarantees both energy savings and accurate color rendition. A die-cast aluminum housing and choice of 5" diameter 3- (1.75X) or 5-diopter (2.25X) lenses ensures the LFM LED Magnifier is well-equipped for any inspection or assembly application. 45" or 30" heavy-duty internal-spring K-arm









- 9.5W dimmable LEDs (10W total power consumption)
- 4000°K color temperature
- Die-cast aluminum housing
- 5" diameter lens
- 3- (1.75X) or 5-diopter (2.25X) lens
- 45" or 30" heavy-duty internal-spring K-arm
- Edge clamp or weighted base mount
- Color: Light Grey.

LFM LED Magnifiers

CODES

LFM LED MAGNIFIERS

Article Number	Light Source	Watt	Total Effect	Arm Length	Mount	Diopter Colors
18345LG	LED	9.5	10	45.0/1143	Edge clamp	3 
18346LG	LED	9.5	10	45.0/1143	Edge clamp	5 
18350LG	LED	9.5	10	30.0/762	Edge clamp	3 
18351LG	LED	9.5	10	30.0/762	Weighted base	3 
18352LG	LED	9.5	10	30.0/762	Edge clamp	5 
18353LG	LED	9.5	10	30.0/762	Weighted base	5 

ACCESSORIES

4-diopter STAYS Lens
 6-diopter STAYS Lens
 10-diopter STAYS lens

DESIGNATION

50404
 50406
 50410